

HyperLink Wireless 2.4 GHz 20 dBi 120 Degree Sector Panel Wireless LAN Antenna - Model: HG2420P-120 (Now ANATEL® APPROVED)

Applications and Features

Applications:

- 2.4 GHz ISM Band
- IEEE 802.11b and 802.11g Wireless LAN
- Bluetooth®
- Public Wireless Hotspot
- WiFi
- Wireless Video Systems
- Wireless Internet Provider "cell" sites

Features:

- Superior performance
- All weather operation
- 120° beam-width
- 20° Down-Tilt Mounting Bracket
- Includes Mast Mounting Hardware
- Integral N-Female Connector
- RoHS Compliant



Description

Superior Performance

The HyperGain® HG2420P-120 Sector Panel WiFi Antenna combines very high gain with a wide 120° beam-width. It is a professional quality "cell site" antenna designed primarily for service providers in the 2.4GHz ISM band. Applications include IEEE 802.11b and 802.11g wireless LAN systems.

ANATEL® APPROVED

This antenna has been homologated (tested) in Brazil and is ANATEL® APPROVED for all installations in Brazil. This is another antenna in a series of L-com antennas certified for installation and use throughout Brazil.

Rugged and Weatherproof

This antenna features a heavy-duty plastic radome for all-weather operation. The mounting system adjusts from 0 to 20 degrees down-tilt.

Ideal for Wireless Internet "Cell" Sites

This antenna is an ideal choice for Wireless Internet Provider "cell" sites since the cell size can be easily determined by adjusting the down-tilt angle. Horizontal coverage is a full 120 degrees, and side-radiation is minimized by the heavy-duty aluminum reflector.



Specifications

Electrical Specifications


Frequency	2400-2500 MHz
Gain	20 dBi
Horizontal Beam Width	120 degrees
Vertical Beam Width	+/- 5°
Impedance	50 Ohm
Max. Input Power	250 Watts
VSWR	< 1.3:1 avg.
Connector	N Female
Lightning Protection	DC Short

Mechanical Specifications


Weight	12 lbs. (5.44 Kg)
Dimensions	39 x 9 x 2.5 inches (99 x 22.9 x 6.4 cm)
Radome Material	UV-Inhibited Polymer
Reflector Material	Aluminum
Operating Temperature	-40° C to 85° C (-40° F to 185° F)
Mounting	2 inch (5 cm) O.D. pipe max.
Polarization	Vertical
Downtilt (mech)	0 to 20 degrees (adjustable)
Compliant	ANATEL® Brazil and RoHS

Wind Loading Data

Wind Loading	Front Surface	Side Surface
Area	2.43 sq. ft. (.23 sq. meters)	0.68 (.06 sq. meters)
@ 100 MPH (161 KPH)	79 lbs. (35.8 Kg)	23 lbs. (10.4 Kg)



Vertical



Horizontal

Guaranteed Quality

This product is backed by L-Com's Limited Warranty