


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/14/2023	DZINN	PHOSPODAR

.37<sup>.02</sup>  
-.00  
[9.4<sup>.05</sup>  
0.0]


.38<sup>.02</sup>  
-.00  
[9.6<sup>.05</sup>  
0.0]

MTG HOLE  
1.7mm MAX THK  
REF ONLY




.44  
[11.1]

.38  
[9.5]




.150  
[3.80]



.366±.004  
[9.3±0.1]

1.15  
[29.2]



#### NOTES:

1. ADAPTER SUPPLIED WITH 2 DUST CAPS INSTALLED WHICH ARE NOT SHOWN.
2. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:

$\leq 12$  [305] = +1 [25] / -0

$> 12$  [305]  $\leq 60$  [1524] = +2 [51] / -0

$> 60$  [1524]  $\leq 120$  [3048] = +4 [102] / -0

$> 120$  [3048]  $\leq 300$  [7620] = +6 [152] / -0

$> 300$  [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:

$.X = \pm .2$  [5]

$.XX = \pm .02$  [5]

$.XXX = \pm .005$  [1.3]

FRACTIONS  
 $\pm 1/32$

ANGLES  $\pm 1^\circ$

CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

THIRD-ANGLE PROJECTION

COLOR VARIATIONS  
MAY OCCUR

SIZE

CAGE CODE

ITEM NO.

REV.

SCALE: NONE

CAD FILE: FOA-CS1-01.SLDDRW

SHEET 1 OF 1



50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

FIBER OPTIC

PRODUCT DESCRIPTION  
CS SINGLE CHANNEL (2F) ADAPTER,  
NO FLANGE, BLUE

SIZE A CAGE CODE 43321 ITEM NO. FOA-CS1-01 REV. A