


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION				
ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	A	INITIAL RELEASE	04/28/2023	KGLEBOVA
				GUTTADAURO



NOTES:

MECHANICAL DATA:


1. CONDUCTOR SIZE: 26AWG - 28AWG.
7 STRANDED, ANNEALED COPPER WIRE.
2. INSULATION O.D.: 0.95mm TO 1.05mm.
3. BRAID SHIELD: TIN PLATING.
4. CABLE O.D.: $\phi 6.3\text{mm}$ TO $\phi 7.2\text{mm}$.

MISCELLANEOUS:

5. THIS DRAWING SHOWS IX30G-B-10S-CVL1(7.0).
6. THIS PRODUCT (TYPE B) IS USED FOR NON ETHERNET APPLICATIONS LIKE SIGNALING, SERIAL OR OTHER INDUSTRIAL BUS COMMUNICATION SYSTEMS. PLEASE USE TYPE A FOR 10/100 MBIT/S AND 1/10 GBIT/S ETHERNET COMMUNICATION.
7. PRODUCT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
8. SHIPS UNASSEMBLED AND SHIELD SHELL IS PRE-BENT.

EXPLODED VIEW

PART TABLE	
ITEM	DESCRIPTION
1	COVER CASE
2	GUIDE
3	SHIELD SHELL
4	PLUG UNIT
5	SHIELD CASE
6	COVER CASE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS	DATE	 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY KGLEBOVA	04/12/2023			
	CHECKED BY BPUCHASKI	04/17/2023			
	APPROVED BY GUTTADAURO	04/20/2023			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM / MODULAR		
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION IX INDUSTRIAL RIGHT ANGLE PLUG, 10gig, B KEY, 90° DOWN DESIGN, IDC CRIMP TYPE, 26-28AWG RANGE		
	SIZE A	CAGE CODE 43321	ITEM NO. IXP-C2628RAD-B	REV. A	
		SCALE: NONE	CAD FILE: ixp-c2628rad-b.SLDDRW		SHEET 1 OF 1