

6

5


4

3

2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-15015	10/03/2025	DMAY	DGUTTADAURO



NOTES:

ELECTRICAL:

- NOMINAL VOLTAGE: 300 V.
- OPERATING VOLTAGE: 60 V DC/AC MAX.
- OPERATING CURRENT PER CONTACT: 4 A MAX.

APPLICATION:

- INGRESS PROTECTION RATING IS IP67 (MATED)
- RECOMMENDED TORQUE VALUE: 0.6 Nm
- BEND RADIUS FIXED: 38.4 mm MIN.
- BEND RADIUS MOBILE: 72 mm MIN.

ENVIRONMENTAL:

- TEMPERATURE RANGE FIXED: -25°C TO +80°C
- TEMPERATURE RANGE MOBILE: -25°C TO +70°C
- CABLE JACKET RESISTANCE: OIL
- CABLE JACKET FLAME RATING: HB (UL 94).

MISCELLANEOUS

- CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENTLY RELEASED VERSION).

P1	WIRE MAP	P2
BROWN 1		1 BROWN
WHITE 2		2 WHITE
BLUE 3		3 BLUE
BLACK 4		4 BLACK
GRAY 5		5 GRAY

ITEM NO	LENGTH [TOL.]	
	METERS [mm]	FEET [IN]
TRGA502-P2N-05M	0.5 [+35/-15]	1.64 [+1.38/- .59]
TRGA502-P2N-1M	1 [+35/-20]	3.28 [+1.38/- .79]
TRGA502-P2N-2M	2 [+35/-30]	6.56 [+1.38/-1.18]
TRGA502-P2N-3M	3 [+35/-30]	9.84 [+1.38/-1.18]
TRGA502-P2N-5M	5 [±60]	16.40 [±2.36]
TRGA502-P2N-10M	10 [±80]	32.81 [±3.15]
TRGA502-P2N-15M	15 [±80]	49.21 [±3.15]

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6

5

4

3

2

1