


8 7 6 5 4 3 2 1  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/08/2023	BPUCHASKI	AGANWANI




NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 <b>CATEGORY</b> COAXIAL	
OVERALL CABLE LENGTH TOLERANCE:	DRAWN BY BPUCHASKI	05/08/2023		
$\leq 12$ [305] = +1 [25] / -0	CHECKED BY KLEITLEIN	05/08/2023		
$> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0	APPROVED BY AGANWANI	05/08/2023		
$> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0	<b>PRODUCT DESCRIPTION</b> BNC Male to BNC Male Right Angle Cable Using RG316 Coax			
$> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0				
$> 300$ [7620] = +5% / -0	ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5]      FRACTIONS $.XX = \pm .02$ [.5] $\pm 1/32$ $.XXX = \pm .005$ [.13]      ANGLES $\pm 1^\circ$ <b>THIRD-ANGLE PROJECTION</b> 			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR		
	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>LCCA31346</b>	
	SCALE: NONE	CAD FILE: LCCA31346.SLDDRW	REV. <b>A</b>	
			SHEET 1 OF 1	