




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	04/09/03	MCCORMICK
B	ECN #1818 REVISED LENGTH	08/03/04	MCCORMICK
C	ECN 3112: UPDATE DWG FORMAT	12/12/07	D.GRIFFIN



BNC PLUG

SPECIFICATIONS;

**MATERIALS;**

BODY: BRASS  
REAR TUBE: BRASS  
CONTACTS: BRASS  
INSULATOR: PTFE

**FINISH;**

BODY: NICKEL PLATE  
REAR TUBE: NICKEL PLATE  
CONTACT: GOLD PLATE

**ELECTRICAL;**

CHARACTERISTIC IMPEDANCE: 75 OHM UNBALANCED  
COAXIAL TO 120 OHM BALANCED TWISTED PAIR

**ENVIRONMENTAL;**


OPERATING TEMPERATURE RANGE: -10°C TO 75°C

**APPLICATION NOTES:**

0.020" TO 0.026" CONDUCTOR DIAMETER, STP OR UTP  
INSULATION FROM 0.028" TO 0.60"

CABLE ENTRY DIAMETER: 0.193" MIN

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  TOLERANCES TO BE: .X ±.1 [2.5]      ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13]  OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 > 60 [1524] +5% / -0%	APPROVALS		DATE	L-com CONNECTIVITY PRODUCTS	01845	CATEGORY	PRODUCT DESCRIPTION  75-120 OHM BNC PLUG COMPRESSION IDC	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO.  ACC8060	REV. <b>C</b>
	DRAWN BY C.MCCORMICK		04/09/2003								
	CHECKED BY D.PARHAM		04/09/2003								
	APPROVED BY R.CARRICK		04/09/2003								
PROJ 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			SCALE: NONE		CAD FILE: ACC8060.SLDDRW		SHEET 1 OF 1			