


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	11/13/01	MCCORMICK
B	ECN# 2231 ADDED COMPONENT SPECIFICATION & REF DOCUMENTS	12/23/05	MCCORMICK
C	ECN 3167: UPDATE DWG FORMAT	1/25/08	D.GRIFFIN
D	ECN 4448: REVISED DRAWING AND NEW FORMAT	12/18/09	D.FRISIELLO


DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
FERRULE	BRASS OR COPPER ALLOY	NICKEL PLATE
PIN	BRASS	GOLD PLATE
INSULATOR	ACETAL	-




FERRULE




PIN



BODY



RECOMMENDED  
FERRULE & PIN  
CRIMP SIZES



RECOMMENDED  
CABLE STRIPPING  
DIMENSIONS

NOTES:

**ELECTRICAL:**  
IMPEDANCE: 75 OHM

**PACKAGING:**  
COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**APPLICATION:**  
THIS CONNECTOR IS FOR USE ONLY WITH RG59 CABLE WITH SOLID CENTER CONDUCTOR.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°  PROJECTION	APPROVALS DRAWN BY MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 11/13/01 11/13/01 11/13/01		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY COAXIAL		PRODUCT DESCRIPTION CONN TNC M RG59 CRIMP		
	COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. BAC893-59
	SCALE: NONE		CAD FILE: BAC893-59.SLDDRW		REV. <b>D</b> SHEET 1 OF 1