


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/19/10	D.GRIFFIN





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMRTMAXXX	WHERE XXX = LENGTH IN FEET	CA-NMRTMA010 (10 FEET)
CA-NMRTMANXX	WHERE NXX = LENGTH IN INCHES	CA-NMRTMAN16 (16 INCHES)
CA-NMRTMAMXX	WHERE MXX = LENGTH IN METERS	CA-NMRTMAM07 (7 METERS)
CA-NMRTMAXMX	WHERE XMX = LENGTH IN DECIMAL METERS	CA-NMRTMA3M5 (3.5 METERS)

RoHS Compliant ✓

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	3/19/10		CATEGORY COAXIAL
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY C.BRAN	3/19/10	PRODUCT DESCRIPTION CA, CA195 N-M RA/TNC M	
	APPROVED BY K.BURGNER	3/19/10		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. CA-NMRTMA	REV. A
SCALE: NONE		CAD FILE: CA-NMRTMA.SLDDRW		SHEET 1 OF 1