


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/15/10	D.GRIFFIN



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-QPRQPRA $\underline{\text{XXX}}$	WHERE XXX = LENGTH IN FEET	CA-QPRQPRA010 (10 FEET)
CA-QPRQPRAN $\underline{\text{XX}}$	WHERE NXX = LENGTH IN INCHES	CA-QPRQPRAN16 (16 INCHES)
CA-QPRQPRAM $\underline{\text{XX}}$	WHERE MXX = LENGTH IN METERS	CA-QPRQPRAM07 (7 METERS)
CA-QPRQPRA $\underline{\text{XMX}}$	WHERE XMX = LENGTH IN DECIMAL METERS	CA-QPRQPRA3M5 (3.5 METERS)

- NOTE:
1. CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
  2. CABLE ASSEMBLIES TO BE PACKAGED INDIVIDUALLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D. PARHAM CHECKED BY C. BRAN APPROVED BY K. BURGNER	DATE 03/12/2010 03/12/2010 03/12/2010	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY <b>COAXIAL CABLES</b> PRODUCT DESCRIPTION <b>CA,CA-195 QMA RA PLUG/PLUG</b>		
PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CA-QPRQPRA</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: CA-QPRQPRA.SLDDRW		SHEET 1 OF 1