


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/2/12	D.GRIFFIN
B	ECN 8654: REVISE DESCRIPTION TYPE-N PLUG TO TNC PLUG, FORMAT, ROHS	2/24/17	D.FRISIELLO



TYPE N-MALE  
RIGHT ANGLE  
CONNECTOR

LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA4NMRRTP $\underline{XXX}$	WHERE XXX = LENGTH IN FEET	CA4NMRRTP010 (10 FEET)
CA4NMRRTP $\underline{NXX}$	WHERE NXX = LENGTH IN INCHES	CA4NMRRTPN16 (16 INCHES)
CA4NMRRTP $\underline{MXX}$	WHERE MXX = LENGTH IN METERS	CA4NMRRTPM07 (7 METERS)
CA4NMRRTP $\underline{XMX}$	WHERE XMX = LENGTH IN DECIMAL METERS	CA4NMRRTP3M5 (3.5 METERS)

**B** TNC PLUG  
REVERSE POLARITY  
STRAIGHT CRIMP  
CONNECTOR

- NOTES:**
1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
  3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [51] .XXX = $\pm .005$ [13]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY T.VADEN APPROVED BY P.PESA	DATE 8/1/12 8/1/12 8/1/12	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY COAXIAL
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
	DWG. NO. CA4NMRRTP		REV. <b>B</b>	SCALE: NONE   CAD FILE: CA4NMRRTP.SLDDRW   SHEET 1 OF 1