


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN RELEASE	1/26/10	D.GRIFFIN
B	ECN 9071: UPDATE DIM'S AND NOTES	02/10/18	S.LI

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL
INSULATOR	PTFE (WHITE)	-
SLEEVE	BRASS	NICKEL
FERRULE	BRASS	NICKEL
CONTACT PIN	PHOSPHOR BRONZE	GOLD



NOTES:

ELECTRICAL:
 IMPEDANCE: 75 OHMS
 FREQUENCY RANGE: DC~4GHz
 CONTACT RESISTANCE: CENTER PIN IS LESS THAN 1 MOHMS AND OUTER CONTACT IS LESS THAN 3 MOHM.
 INSULATION RESISTANCE: 5000 MOHMS.
 VOLTAGE WITHSTAND: 1500 V
 OPERATING TEMPERATURE: -30~+85°C

MECHANICAL:
 DURABILITY: 500 CYCLES.

MISCELLANEOUS:
 COMPONENTS SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
 CE2011/65/EU (ROHS DIRECTIVE)

RECOMMENDED FERRULE & PIN CRIMP SIZE

RECOMMENDED CABLE STRIPPING

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 [2.54] .XX = ±.01 [25] .XXX = ±.005 [13]	APPROVALS	DATE			50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY D. CASTRO	1/26/10			CATEGORY	COAXIAL
	CHECKED BY D. FRISIELLO	1/26/10	PRODUCT DESCRIPTION	BNC JACK 75 OHM RG179 CRIMP		
	APPROVED BY P. MCNEIL	1/26/10	SIZE	FSCM NO.	DWG. NO.	REV.
ANGULAR TOLERANCES: ALL = ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		A	43321	BAC549	B
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: BAC549.SLDDRW	SHEET 1 OF 1	