






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/29/2022	Guttadauro



WIRING MAP	
P1	P2
A2	B11
A3	B10
B11	A2
B10	A3
A10	B3
A11	B2
B3	A10
B2	A11
A5	A5
B5	B5
B8	A8
A8	B8
A6	A6
A7	A7
A1, B1, A12, B12 SHELL	A1, B1, A12, B12 SHELL
A4, B4, A9, B9	A4, B4, A9, B9

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - PASS 240W (48V5A) 40G 4K@60Hz 5K@60Hz 8K@60Hz TEST.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY RCARLESCO APPROVED BY Guttadauro	DATE 11/29/2022 11/29/2022 11/29/2022	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY USB		PRODUCT DESCRIPTION USBC 4.0-40G/240W, M-M, Metal Cable
THIRD-ANGLE PROJECTION 	SIZE A	CAGE CODE 43321	ITEM NO. CAU4CC-40MC	REV. A
SCALE: NONE		CAD FILE: CAU4CC-40MC.SLDDRW		SHEET 1 OF 1