


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/05/2002	MCCORMICK
B	ECN#2087: ADDING OHM VALUE	05/24/05	M.LAHEY
C	ECN 3253: UPDATE DWG FORMAT	4/8/08	D.GRIFFIN



MODEL #	LENGTH	
	FEET	METERS
CC6PB-1	1.0	0.31
CC6PB-1.5	1.5	0.46
CC6PB-2	2.0	0.61
CC6PB-2.5	2.5	0.76
CC6PB-5	5.0	1.52
CC6PB-7.5	7.5	2.29
CC6PB-10	10.0	3.05
CC6PB-15	15.0	4.57

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY INDIVIDUALLY PACKAGE IN A POLYBAG

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2[51] / -0 > 60 [1524] ≤ 120 [3048] = +4 / -0 > 120 [3048] ≤ 300 [7620] = +6 / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS DRAWN BY P.LECLAIR	DATE 11/18/2002		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CHECKED BY C.MCCORMICK	DATE 11/26/2002		CATEGORY COAXIAL	
	APPROVED BY D.PARHAM	DATE 11/26/2002	PRODUCT DESCRIPTION RG6 PLEN CBL BNC M/M		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CC6PB	REV. C