


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
E	ECN 4118: CN RELEASE AND NEW FORMAT	7/13/09	D.FRISIELLO
E	ECN 99999: REVISED "P1" VIEW FOR OFFSET	10/9/09	D.FRISIELLO
F	ECN 4690: CHANGED UL STYLE FROM 20276 TO 2990	4/19/10	D.FRISIELLO



MALE 68 PIN PICO RIBBON CONNECTOR (0.8mm PITCH)

MALE 50 PIN MICRO D-SUB CONNECTOR (.050" PITCH)

WIRING TABLE					
CN68M	PAIR	HPDB50M	CN68M	PAIR	HPDB50M
6	1	1	19	13	14
40		26	53		39
7	2	2	20	14	15
41		27	54		40
8	3	3	21	15	16
42		28	55		41
9	4	4	22	16	17
43		29	56		42
10	5	5	23	17	18
44		30	57		43
11	6	6	24	18	19
45		31	58		44
12	7	7	25	19	20
46		32	59		45
13	8	8	26	20	21
47		33	60		46
14	9	9	27	21	22
48		34	61		47
15	10	10	28	22	23
49		35	62		48
16	11	11	29	23	24
50		36	63		49
18	12	13	30	24	25
52		38	64		50

MODEL NUMBER	LENGTH	
	METERS	FEET
CA2051MM-05M	0.5	1.64
CA2051MM-1M	1.0	3.28
CA2051MM-2M	2.0	6.56
CA2051MM-3M	3.0	9.84

- NOTES:**
- CABLE DRAIN WIRE CONNECTED TO METAL FRAME OF EACH CONNECTOR.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

DRAIN WIRE CONNECTED TO METAL FRAME OF EACH CONNECTOR

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 OVERALL CABLE LENGTH TOLERANCE:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2[51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0%
 ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ±.2
 .XX = ±.02
 .XXX = ±.005

APPROVALS	DATE
DRAWN BY D PARHAM	8/13/2001
CHECKED BY T CLARK	8/14/2001
APPROVED BY R CARRICK	8/15/2001

L-com Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845

CATEGORY: DATA CABLING

PRODUCT DESCRIPTION: CA, SCSI15, .8mmCN68M/HP50M

SIZE: **B** FSCM NO. **43321** DWG. NO. **CA2051MM** REV. **F**

SCALE: 1:1 CAD FILE: CA2051MM.SLDDRW SHEET 1 OF 1

D
C
B
A

D
C
B
A

8

7

6

5

4

3

2

1

8

7

6

5

4

3

2

1