



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
	INITIAL RELEASE	4/7/03	R. CARRICK
B	ECN 41 67: CN RELEASE AND NEW FORMAT	8/4/09	D. FRISIELLO



MODEL #	DESCRIPTION	LENGTH	TENSILE STRENGTH	MAX BUNDLE DIAMETER	QUANTITY
CTB-05	NYLON 6/6 CABLE TIE	6"	40 lbs.	1.25"	100/PKG
CTB-07	NYLON 6/6 CABLE TIE	8"	50 lbs.	2.0"	100/PKG
CTB-09	NYLON 6/6 CABLE TIE	8.5"	40 lbs.	2.50"	100/PKG
CTB-12	NYLON 6/6 CABLE TIE	11.5"	40 lbs.	3.0"	100/PKG



** ALL CABLE TIE LENGTHS AND BUNDLE DIAMETERS LISTED ARE APPROXIMATE.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 / -0 > 120 [3048] ≤ 300 [7620] = +6 / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± 0.3 .XX = ± 1.5	APPROVALS DRAWN BY R. CARRICK	DATE 4/3/2003	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CHECKED BY D. PARHAM	4/3/2003		CATEGORY HARDWARE		
	APPROVED BY C. MCCORMICK	4/3/2003	PRODUCT DESCRIPTION CABLE TIE			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CTB-05
SCALE: 1:1		CAD FILE: CTB-05.SLDDRW		SHEET 1 OF 1		