


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	APPROVED FOR PRODUCTION BY: S.SMITH	11/11/03	B.MAZEJKA
B	ECN 3332: CN RELEASE	5/16/08	D.CASTRO
C	ECN 6749: UPDATED FORMAT, PACKAGING, & LOGOS. ADDED PANTONE #'S	3/22/13	D. DESJARDIN
D	ECN 9971: REMOVE PIN MARKING FROM BOTH CONNECTOR FACES P1 and P2. REMOVED ROHS COMPLIANT STATEMENT.	07/15/2019	B.GATES



WIRING MAP		
P1	COLOR	J1
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	LT. GREEN	6
SHELL	DRAIN	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CSMD6MM-3	3.0	.91
CSMD6MM-6	6.0	1.83
CSMD6MM-10	10.0	3.05
CSMD6MM-25	25.0	7.62

NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2[5.08] .XX = ± .02[.51] .XXX = ±.005[.13]	APPROVALS DRAWN BY B.MAZEJKA CHECKED BY C.McCORMICK APPROVED BY D.PARHAM	DATE 11/07/2003 11/07/2003 11/07/2003	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY <b>I/O PRODUCTS</b>	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION <b>CBL,MD6M/M SHLD</b>	
	PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CSMD6MM</b>

SCALE: NONE | CAD FILE: CSMD6MM.SLDDRW | SHEET 1 OF 1