


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-M2SR-SCSC-01M	1.0 [3.28]
FCA-M2SR-SCSC-02M	2.0 [6.56]
FCA-M2SR-SCSC-03M	3.0 [9.84]
FCA-M2SR-SCSC-05M	5.0 [16.40]
FCA-M2SR-SCSC-10M	10.0 [32.81]
FCA-M2SR-SCSC-15M	15.0 [49.21]

**NOTES:**

- SC CONNECTOR ASSEMBLY POLISH TYPE: UPC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:  <math>\leq 12</math> [305] = +1 [25] / -0  <math>&gt; 12</math> [305] <math>\leq 60</math> [1524] = +2 [51] / -0  <math>&gt; 60</math> [1524] <math>\leq 120</math> [3048] = +4 [102] / -0  <math>&gt; 120</math> [3048] <math>\leq 300</math> [7620] = +6 [152] / -0  <math>&gt; 300</math> [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES:  .X = <math>\pm .2</math> [5]      FRACTIONS <math>\pm 1/32</math>  .XX = <math>\pm .02</math> [.5]      ANGLES <math>\pm 1^\circ</math>  .XXX = <math>\pm .005</math> [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	<p>APPROVALS</p> <p>DRAWN BY: MVEERAPPAN</p> <p>CHECKED BY: DFRISIELLO</p> <p>APPROVED BY: PHOSPODAR</p>	<p>DATE</p> <p>09/28/2021</p> <p>09/28/2021</p> <p>09/28/2021</p>	<p>an INFINITO brand</p> <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>		
	<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p>	<p>CATEGORY</p> <p>FIBER OPTICS</p> <p>PRODUCT DESCRIPTION</p> <p>CA SC-SC 50/125 MULTIMODE</p>	<p>SIZE</p> <p><b>A</b></p> <p>SCALE: NONE</p>	<p>CAGE CODE</p> <p><b>43321</b></p> <p>CAD FILE: FCA-M2SR-SCSC.SLDDRW</p>	<p>ITEM NO.</p> <p>FCA-M2SR-SCSC</p>