


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	10/25/2023	DFRISIELLO	PHOSPODAR



FIBER PERFORMANCE

INDUSTRY STANDARD	OM4 LASER OPTIMIZED BEND INSENSITIVE (ISO/IEC 11801)
CORE/CLADDING DIAMETER (μm)	50/125
WAVLENGTH (nm)	850/1310
GIGABIT ETHERNET DISTANCE (M)	1040/600
10-GIGABIT ETHERNET DISTANCE (M)	550/300
PRIMARY COATING DIAMETER (μm)	245
SECONDARY BUFFER DIAMETER (μm)	900

INSTALLATION AND OPERATING CHARACTERISTICS

	INSTALLATION	OPERATING
MAX. TENSILE LOAD	600 N (135 lbs)	300 N (67 lbs)
MIN. BEND RADIUS	3.8 cm (1.5 in)	2.5 cm (1.0 in)

MECHANICAL AND ENVIRONMENTAL

FLEX RESISTANCE TIA-455-104	1,000 CYCLES
CRUSH RESISTANCE TIA-455-41	500 N/cm
OPERATING TEMPERATURE	-40 °C TO +70 °C
STORAGE TEMPERATURE	-40 °C TO +70 °C

CABLE CHARACTERISTICS

JACKET COLOR	AQUA 10 GIG
JACKET MATERIAL	LOW SMOKE ZERO HALOGEN
BUFFER MATERIAL	HARD ELASTOMERIC
CABLE DIAMETER	2.0 x 4.5 mm (0.08 x 0.18 in)

ITEM NUMBER	LENGTH/TOL.
FCA-MSTMSTM4DXLS-05	5.0 METERS +0.15M/0
FCA-MSTMSTM4DXLS-10	10.0 METERS +0.3M/0
FCA-MSTMSTM4DXLS-15	15.0 METERS +0.3M/0
FCA-MSTMSTM4DXLS-20	20.0 METERS +0.3M/0

NOTES:

- ALL CABLE ASSEMBLIES TO BE SUPPLIED WITH A TEST REPORT.
- IDENTIFICATION LABELS ARE YELLOW M23053/5.
- CABLE ASSEMBLY IS PACKAGED HAND COILED.
- FABRICATED, INSPECTED, AND TESTED IAW IPC-A-640, CLASS 3.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS


TOLERANCES:
 X = ±2 [5] FRACTIONS ± 1/32
 .XX = ±0.02 [0.5] ANGLES ± 1°
 .XXX = ±0.005 [0.13]

CABLE LENGTH TOLERANCES:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤ 60 [1524] = +2 [51] / -0
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UN-DIMENSIONED (NON-CRITICAL) FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.

L-com
 an INFINIT® brand

Website: www.L-com.com
 Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION
 2X ST-MIL C-83522 CONNECTOR TO 2X ST-MIL C-83522, MM, OM4, 2.0mm LSZH

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DFRISIELLO	FCA-MSTMSTM4DXLS	A