


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 2819: RE-DRAWN AND REVISED	4/19/07	D.FRISIELLO
C	ECN 2846: CHG DIM .41 TO .37 W/TOL	5/10/07	D.FRISIELLO
D	ECN3064: ADDED NOTES AND REVISED <50 TO ≤55	10/29/07	D.FRISIELLO
E	ECN3399: CHNGD DIMS TO REF	06/19/08	D. PARHAM



MODEL	ATTENUATION	BACK REFLECTION
FOATSTU-05D	5dB	< -50dB
FOATSTU-10D	10dB	< -50dB
FOATSTU-15D	15dB	< -50dB
FOATSTU-20D	20dB	< -50dB
FOATSTU-25D	25dB	< -50dB

ALL DIMENSIONS FOR REFERENCE ONLY

- NOTES
1. ATTENUATOR UTILIZES "UPC" POLISH.
 2. ATTENUATOR IS PACKAGED WITH DUST CAPS INSTALLED (NOT SHOWN)
 3. OPERATING TEMPERATURE RANGE: -40° C TO +75° C.
 4. SINGLEMODE WAVELENGTH RANGE: 1310-1550 nm.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	4/18/07	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	CHECKED BY P.McNEIL	4/18/07	CATEGORY FIBER OPTICS
	ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVED BY P.McNEIL	4/18/07
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A FSCM NO. 43321 DWG. NO. FOATSTU REV. E
SCALE: NONE		CAD FILE: FOATSTU.SLDDRW	
			SHEET 1 OF 1