



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/02/02	MCCORMICK
B	ECN# 2248 CONSTRUCTION FROM 1.6mm TO 3.0mm	11/10/05	MCCORMICK



**NOTES:**

- 1.0 TEST:**  
 1.1 INSERTION LOSS TESTED AT 1300nm WITH A <-1.0 dB RESULT.
- 2.0 PACKAGING:**  
 2.1 THE PRODUCT SHALL BE PRESERVED & PACKAGED IN A MANNER WHICH WILL AFFORD ADEQUATE PROTECTION AGAINST CORROSION, DETERIORATION, AND PHYSICAL DAMAGE DURING SHIPMENT.  
 2.2 INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG DEPICTED ON 1AN01-001-OD1 . MARK EACH BAG PER LSP-010-1
- 3.0 WORKMANSHIP:**  
 3.1 CABLE ASSEMBLIES SHALL BE MANUFACTURED IN SUCH A MANNER AS TO BE UNIFORM IN QUALITY AND SHALL BE FREE FROM DEFECTS THAT WILL ADVERSELY AFFECT LIFE, SERVICEABILITY, OR APPEARANCE.
- 4.0 VISUAL AND MECHANICAL:**  
 4.1. CABLE ASSEMBLIES SHALL BE INSPECTED TO VERIFY COMPLIANCE TO THIS DRAWING.
- 5.0 MANUFACTURING:**  
 5.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.



PART NUMBER	LENGTH METER
FODPLC50-01	1.0
FODPLC50-02	2.0
FODPLC50-03	3.0
FODPLC50-04	4.0
FODPLC50-05	5.0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES  
 TOLERANCES ARE:  
 X ±.1  
 XX ±.05  
 XXX ±.005  
 CABLE LENGTH TOLERANCE  
 ≤300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	12/02/2002
CHECKED BY D.PARHAM	12/02/2002
APPROVED BY R.CARRICK	12/02/2002

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

**L-com**  
 CONNECTIVITY PRODUCTS

45 BEECHWOOD DRIVE  
 NORTH ANDOVER, MA  
 01845

PRODUCT DESCRIPTION  
**50/125 LC PLENUM DUPLEX CABLE ASSY**

DRAWING TITLE  
**OUTLINE DRAWING**

SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>FODPLC50-01-OD1</b>	REV. <b>B</b>
SCALE: NONE		CAD FILE: FODPLC50-01-OD1.SLDRW	SHEET 1 OF 1