



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/05	MCCORMICK



**NOTES:**

- 1.0 **TEST:**
  - 1.1 INSERTION LOSS TESTED AT 1300nm WITH A <-1.0 dB RESULT.
- 2.0 **PACKAGING:**
  - 2.1 THE PRODUCT SHALL BE PRESERVED & PACKAGED IN A MANNER WHICH WILL AFFORD ADEQUATE PROTECTION AGAINST CORROSION, DETERIORATION, AND PHYSICAL DAMAGE DURING SHIPMENT.
  - 2.2 INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG DEPICTED ON [1AN01-001-OD1](#) . MARK EACH BAG PER [LSP-010](#).
- 3.0 **WORKMANSHIP:**
  - 3.1 CABLE ASSEMBLIES SHALL BE MANUFACTURED IN SUCH A MANNER AS TO BE UNIFORM IN QUALITY AND SHALL BE FREE FROM DEFECTS THAT WILL ADVERSELY AFFECT LIFE, SERVICEABILITY, OR APPEARANCE.
- 4.0 **VISUAL AND MECHANICAL:**
  - 4.1. CABLE ASSEMBLIES SHALL BE INSPECTED TO VERIFY COMPLIANCE TO THIS DRAWING.
- 5.0 **MANUFACTURING:**
  - 5.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.



PART NUMBER	LENGTH METER
FODSC-10G-01	1.0
FODSC-10G-02	2.0
FODSC-10G-03	3.0
FODSC-10G-04	4.0
FODSC-10G-05	5.0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES  
 TOLERANCES ARE:  
 X ±.1  
 XX ±.05  
 XXX ±.005  
 CABLE LENGTH TOLERANCE  
 ≤300' ±5% >300' ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	12/16/2005
CHECKED BY M.LAHEY	12/16/2005
APPROVED BY D.PARHAM	12/16/2005

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION <b>SC TO SC 50/125 DUPLEX 10 GIG</b>			
DRAWING TITLE <b>OUTLINE DRAWING</b>			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>FODSC-10G-01-OD1</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: FODSC-10G-01-OD1.SLDDRW	SHEET 1 OF 1