



6 5 4 3 2 1





REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	7/8/2025	KDANG	DGUST



MICRO USB FEMALE



2X HDMI FEMALE



DATE & SERIAL LABEL

DESCRIPTION:

EXTENDS THE TRANSMISSION DISTANCE UP TO 125 FT@1080P/60Hz WHEN USING 24AWG HDMI CABLE. FULLY AUTOMATIC EQUALIZATION UP TO 14DB, NO SYSTEM CONTROL REQUIRED.

FEATURES

1. HDCP 1.4 AND HDMI 1.4 COMPLIANT.
2. MICRO USB PORT FOR OPTIONAL EXTERNAL POWER INPUT.
3. OPERATING TEMPERATURE RANGE: +32 TO +104 DEGREES FAHRENHEIT / 0 TO +40 DEGREES CELSIUS.
4. STORAGE TEMPERATURE RANGE: +5 TO +122 DEGREES FAHRENHEIT / -15 TO +50 DEGREES CELSIUS.
5. RELATIVE HUMIDITY: 0 TO 85%, NON-CONDENSING.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ± 2 [5] FRACTIONS
XX = $\pm .02$ [0.5] $\pm 1/32$
XXX = $\pm .005$ [0.13] ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:
 ≤ 12 [305] = ± 1 [25] / -0
 > 12 [305] ≤ 60 [1524] = ± 2 [51] / -0
 > 60 [1524] ≤ 120 [3048] = ± 4 [102] / -0
 > 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0
 > 300 [7620] = $\pm 5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE[®] brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE SHEET
NONE 1 OF 1

DESCRIPTION
HDMI SIGNAL EXTENDER, 1080P/60HZ RESOLUTION, FEMALE
TO FEMALE, NON-POWER REPEATER

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KDANG	HDRPTR	A