


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/17/20	PHOSPODAR

WIRING MAP

PAIR	LC	1X24	REF DES
P1	1	1	J1
	13	13	
P2	2	2	
	14	14	
P3	3	3	
	15	15	
P4	4	4	
	16	16	
P5	5	5	
	17	17	
P6	6	6	
	18	18	
P7	7	7	
	19	19	
P8	8	8	
	20	20	
P9	9	9	
	21	21	
P10	10	10	
	22	22	
P11	11	11	
	23	23	
P12	12	12	
	24	24	



PART NUMBER	METERS (FEET)
MPF24OM4-20LCR-1	1.0 (3.28)
MPF24OM4-20LCR-3	3.0 (9.84)
MPF24OM4-20LCR-5	5.0 (16.40)
MPF24OM4-20LCR-10	10.0 (32.81)

- NOTES:
1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5] FRACTIONS $\pm 1/32$.XX = $\pm .02$ [.5] ANGLES $\pm 1^\circ$.XXX = $\pm .005$ [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	<p>APPROVALS</p> <p>DATE</p>	<p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>
	<p>DRAWN BY DFRISIELLO</p> <p>CHECKED BY PHOSPODAR</p> <p>APPROVED BY PHOSPODAR</p>	
<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p>		<p>CATEGORY</p> <p>FIBER OPTICS</p>
<p>PRODUCT DESCRIPTION</p> <p>MPO w/o pins to LC fanout fiber, 2.0mm diameter, 24 fiber, OM4 50/125um</p>		<p>SCALE: NONE CAD FILE: MPF24OM4-20LCR.SLDDRW SHEET 1 OF 1</p>
<p>SIZE</p> <p>A</p>		<p>CAGE CODE</p> <p>43321</p>
<p>ITEM NO.</p> <p>MPF24OM4-20LCR</p>		<p>REV.</p> <p>A</p>