

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL# HMA3-XXXAYY

1st SUFFIX(XXX) = CONNECTOR TYPE


2nd SUFFIX(Y)Y  
CABLE LENGTH(FT)  
01 TO 10 FEET  
(+2 INCH, -0)

NF	N-FEMALE
NM	N-MALE
RSP	RP SMA-PLUG
RSJ	RP SMA-JACK
RTP	RP TNC-PLUG
RTJ	RP TNC-JACK
RNP	RP N-PLUG
RNJ	RP N-JACK
SM	SMA MALE
SF	SMA FEMALE
TM	TNC MALE
TF	TNC FEMALE
BM	BNC MALE
RBP	RP BNC PLUG
RBJ	RP BNC JACK
WM	WAVE RIDER COMPATIBLE TYPE
AM	ORINOCO COMPATIBLE TYPE
QP	QMA PLUG RIGHT ANGLE



EXAMPLE:  
HMA3-NF02

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/09/11	B.PUCHASKI
B	ECN 8740 CABLE LENGTH TOL +1 TO +2 IN CHART	04/26/17	B.PUCHASKI



Ø3.5 [89]

SEE CHART FOR  
CONNECTOR TYPE

Ø.195 BLACK  
COAX CABLE  
SEE CHART FOR  
CABLE LENGTH

NOTES:


PACKAGING:

COMPONENT SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPEC PKG-00012.

-ALL DIMENSIONS FOR REFERENCE-

REGULATORY COMPLIANCE:  
CE2011/65/EU(RoHS DIRECTIVE)

N-FEMALE  
CONNECTOR



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY B.PUCHASKI	09/09/11		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY P.PESA	09/09/11	PRODUCT DESCRIPTION DOMED MAGNETIC ANTENNA MOUNT W/COAX CABLE AND CONNECTOR	
	APPROVED BY P.PESA	09/09/11	SIZE <b>A</b>	FSCM NO. <b>43321</b>
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	DWG. NO. HMA3-XXXAYY	REV. <b>B</b>
SCALE: NONE		CAD FILE: HMA3-XXXAYY.SLDDRW		SHEET 1 OF 1