


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	06/06/2023	DFRISIELLO	PHOSPODAR

STRUCTURE:	VALUE:
CORE DIAMETER	980 μm (NOM.)
CORE MATERIAL	POLYMETHYL METHACRYLATE RESIN (PMMA)
CLADDING DIAMETER	1,000 μm (NOM.)
CLADDING MATERIAL	FLUORINATED POLYMER
JACKET DIAMETER	2.20 mm X 4.40 mm (NOM.)
JACKET MATERIAL, COLOR	CHLORINATED POLYETHYLENE, BLACK
INDICATION ON JACKET	BLUE LINE
CORE REFRACTIVE INDEX	1.49
REFRACTIVE INDEX PROFILE	STEP INDEX
NUMERICAL APERTURE	0.5





(DRAWING NOT TO SCALE)

PERFORMANCE:			VALUE
OPERATION TEMPERATURE			-55°C ~ 85°C
OPERATION TEMPERATURE WITH HUMIDITY			75°C MAX.
OPTICAL PROPERTIES	TRANSMISSION LOSS (650nm COLLIMATED LIGHT)	25°C @50%RH	170dB/km MAX.
		OPERATING TEMP.	190dB/km MAX.
MECHANICAL CHARACTERISTICS	MINIMUM BEND RADIUS	LOSS INCREMENT ≤ 0.5dB	25mm MIN.
	REPEATED BEND ENDURANCE	LOSS INCREMENT ≤ 1dB	10,000 MIN.
	TENSILE STRENGTH	TENSILE PERFORMANCE TEST EQUIPMENT	140N MIN.
	TWISTING ENDURANCE	LOSS INCREMENT ≤ 1dB (TENSILE FORCE: 4.9N)	2 MIN.
	IMPACT ENDURANCE	LOSS INCREMENT ≤ 1dB (JIS C 6861)	0.4N*m (MIN.)

ITEM NUMBER	LENGTH, METERS [FEET]
LCGHCP4002-25M	25.0 [82.03]
LCGHCP4002-50M	50.0 [164.05]
LCGHCP4002-100M	100.0 [328.10]

NOTES:

- BULK FIBER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY	05/22/2023		CATEGORY FIBER OPTIC
	CHECKED BY	05/22/2023		
	APPROVED BY	05/22/2023		
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION		
	COLOR VARIATIONS MAY OCCUR	Mitsubishi ESKA® GHCP4002, 1x2.2mm Cable, POF Duplex		
		SIZE	REV.	
		A	A	
		CAGE CODE	ITEM NO.	
		43321	LCGHCP4002	
		SCALE: NONE	SHEET 1 OF 1	
		CAD FILE: LCGHCP4002.SLDDRW		