


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE  
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/30/2023	BPUCHASKI	GUTTADAURO



NOTES:

1. REFERENCE: VOLTAGE RATING 15A/125V
2. APPROVALS: UL APPROVED
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:  
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</div> <div>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 &gt;12 [305] ≤60 [1524] = +2 [51] / -0 &gt;60 [1524] ≤120 [3048] = +4 [102] / -0 &gt;120 [3048] ≤300 [7620] = +6 [152] / -0 &gt;300 [7620] = +5% / -0</div> <div>ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]      FRACTIONS .XX = ±.02 [.5]      ± 1/32 .XXX = ±.005 [.13]      ANGLES ± 1°</div> <div>THIRD-ANGLE PROJECTION </div>	APPROVALS	DATE	<div> an INFINITI® brand</div> <div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div>		
	DRAWN BY BPUCHASKI	05/30/2023			
	CHECKED BY DGUST	05/30/2023	CATEGORY		
	APPROVED BY GUTTADAURO	05/30/2023	POWER CORD		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION N5-15P/C19, Industrial STJOW Cord, 125V, 15A			
COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. OWN515C19-15	REV. A
		SCALE: NONE    CAD FILE: OWN515C19-15.SLDDRW			SHEET 1 OF 1