


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN INITIAL RELEASE	03/04/2020	GUTTADAURO



NOTES:

MATERIAL:

CONTACTS: PHOSPHOR BRONZE.
 CABLE JACKET: THERMOPLASTIC ELASTOMER, COLOR: GREEN

FINISH:

CONTACTS: GOLD IN CONTACT AREA OVER NICKEL PLATE OVERALL.

M12 CONNECTOR CHARACTERISTICS:

PROTECTION: IP65/IP67 (WHEN MATED AND TIGHTENED, EN 60529)
 NOMINAL VOLTAGE: MAX 50 V AC/DC
 RATED CURRENT: MAX 4A PER CONTACT
 CATEGORY: CATEGORY 5E (IEC 11801)

CABLE CHARACTERISTICS:

CAT 5e, SHIELDED TWO TWISTED PAIRS,
 22 AWG SOLID TINNED COPPER CONDUCTORS WITH FILLER
 AND WRAPPED WITH A FOAM POLYPROPYLENE TAPE.
 AN OVERALL SHIELD OF 38 AWG TINNED COPPER BRAID (75% MIN.),
 A SECOND SHIELD OF ALUMINIZED POLYESTER FOIL (100%).

OVERALL CABLE DIAMETER NOM.: .305 [7.747]

APPROVALS: UL AWM STYLE 2463 (80C 600V)

NEC (UL) TYPE PLTC

NEC (UL) TYPE ITC

PENNSYLVANIA D.E.P. - MSHA


EU CE MARK: MEETS EU DIRECTIVE 2011/65/EU (RoHS II)

VOLTAGE RATING: 600V



RESISTANCE: OIL, UV AND WELD SPLATTER

MISCELLANEOUS:

OPERATING TEMPERATURE RANGE: -40°C TO +68°C.
 CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN
 ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



PART NUMBER	LENGTH METERS
TRGPA402-05M	0.5
TRGPA402-1M	1.0
TRGPA402-2M	2.0
TRGPA402-3M	3.0
TRGPA402-5M	5.0
TRGPA402-10M	10.0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCES: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
	DRAWN BY DCUI	02/29/2020				
CHECKED BY SPAN	02/29/2020	CATEGORY TELECOM/MODULAR				
APPROVED BY GUTTADAURO	02/29/2020	PRODUCT DESCRIPTION PROFINET C5E RJ45/M124DM SF/UTP PLTC TPE GRN				
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	DWG. NO. TRGPA402	REV. A
SCALE: NONE		CAD FILE: TRGPA402.SLDDRW		SHEET 1 OF 1		