


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/06/18	JLABOY





"P1"  
 PIN 5      PIN 9  
 PIN 4      PIN 1

2X, USB3.0 SERIES "A"  
 LATCHING PLUG  
 CONTACTS: 30 μINCHES  
 GOLD PLATING

"P2"  
 PIN 5      PIN 9  
 PIN 4      PIN 1

PART NUMBER	LENGTH METERS [FEET]
U3A00028-03M	0.3 [.98]
U3A00028-05M	0.5 [1.64]
U3A00028-075M	0.75 [2.46]
U3A00028-1M	1.0 [3.28]
U3A00028-105M	1.5 [4.92]



RECOMMENDED SIDE NOTCH SIZE FOR MATING A FEMALE CONNECTOR

**CABLE:**  
 UL STYLE 21551, 2X, TWISTED PAIR, 30AWG WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE. ONE UNSHIELDED TWISTED PAIR, 30AWG. 2 COND., 24AWG. OVERALL BRAID SHIELD, 65%  
 JACKET: LSZH, BLACK  
 (NOM DIA. .217"[5.5], TEMPERATURE RANGE:-10~+80 °C)

**NOTES:**  
 1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.  
 2. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.  
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS	DATE
	DRAWN BY S.LI	06/27/17
	CHECKED BY B.ZHANG	06/27/17
	APPROVED BY S.PAN	06/27/17
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR

**L-com** Global Connectivity  
 50 HIGH STREET  
 NORTH ANDOVER, MA 01845

CATEGORY: USB

PRODUCT DESCRIPTION: CA,USB3.0 A/A LATCH LSZH

SIZE: <b>A</b>	FSCM NO.: <b>43321</b>	DWG. NO.: <b>U3A00028</b>	REV.: <b>A</b>
SCALE: NONE		CAD FILE: U3A00028.SLDDRW	SHEET 1 OF 1