


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC., ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/23/12	D.GRIFFIN



NOTES:

MATERIAL: FLAME RETARDANT PLASTIC, UL 94V-0

ELECTRICAL:

MAX INPUT: 1.1Vp-p
 INSERTION LOSS: <1 dB, FREQUENCY RANGE FROM DC TO 8 MHZ

CABLE - BNC:

IMPEDANCE: 75 OHMS AT 1MHz (RG59/U)
 MAX. 25 FT COAX ALLOWED PER END TO END LINK

CABLE - UTP:

24AWG OR LOWER SOLID COPPER TWISTED PAIR WIRE
 IMPEDANCE: 100 OHMS AT 1MHz
 MAX. CAPACITANCE: 20pF/FOOT
 ATTENUATION: 6.6dB/1000 FT AT 1 MHz

ENVIRONMENTAL:

OPERATING TEMPERATURE: 0 TO 55 °C

MISCELLANEOUS:

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D. DESJARDIN	10/17/12				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. FRISIELLO	10/18/12	CATEGORY AUDIO/VIDEO			
	APPROVED BY S. SMITH	10/18/12	PRODUCT DESCRIPTION TOOLESS VIDEO BALUN BNC MALE			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TL-VB-BNC	REV. A
			SCALE: NONE	CAD FILE: TL-VB-BNC.SLDDRW	SHEET 1 OF 1	