

Fiber Optic Transceiver SFP 100M, 2 km reach, 850 nm

FXC-SFP100M-85-SX



Features

- Operating Data Rate up to 125Mbps
- Distance Range 2km
- Pluggable SFP Duplex LC Connector
- Standard Operating Temperature
- MSA Compliant

Applications

- Fast Ethernet
- Enterprise Networks
- Fibre Channel Links

Description

The L-com FXC-SFP100M-85-SX is an SFP form-factor transceiver, supporting 100M data rates. The L-com FXC-SFP100M-85-SX features a 850 nm transmitter and supports 2 km links over multimode fiber. The FXC-SFP100M-85-SX is an MSA-compliant transceiver, compatible with most switch and router platforms. The L-com FXC-SFP100M-85-SX features digital diagnostics for performance monitoring of the transceiver. The L-com FXC-SFP100M-85-SX SFP transceiver is one of thousands of fiber optic connectivity products available from L-com in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for your answers on fiber optic connectivity or other L-com products.

Configuration

Connector 1	LC
Connector Mode	Duplex
Compatibility	MSA

Filter Specifications

Description	Minimum	Typical	Maximum	Units
TX Center Wavelength	830	850	860	nm
TX Spectral Width			0.85	nm
TX Average Output Power	-9.5		-4	dBm
TX Extinction Ratio	8.2			dB
RX Center Wavelength	760		860	nm
RX Receiver Sensitivity			-18	dBm
RX Receiver Overload	-3			dBm


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Fiber Optic Transceiver SFP 100M, 2 km reach, 850 nm FXC-SFP100M-85-SX](#)

Fiber Optic Transceiver SFP 100M, 2 km reach, 850 nm



FXC-SFP100M-85-SX

Small Form-factor Pluggable (SFP) Transceiver MultiSource Agreement (MSA)



Fiber Optic Transceiver SFP 100M, 2 km reach, 850 nm



FXC-SFP100M-85-SX




Figure 1. Diagram of Host Board Connector Block Pin Numbers and Names

Environmental Specifications

Temperature

Operating Range
Storage Range

0 to +70 deg C
-40 to +85 deg C

Notes:

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Fiber Optic Transceiver SFP 100M, 2 km reach, 850 nm

FXC-SFP100M-85-SX



Fiber Optic Transceiver SFP 100M, 2 km reach, 850 nm from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.