




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/20/2017	JLABOY
B	ECN 10289: "MOLDED HOOD" WAS "ALUMINUM METAL HOOD"	01/02/2020	GUTTA DAURO



PART NUMBER	LENGTH	
	METERS	FEET
U3A00057-03M	0.3	0.98
U3A00057-05M	0.5	1.64
U3A00057-1M	1.0	3.28
U3A00057-2M	2.0	6.56
U3A00057-3M	3.0	9.84




NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
VOLTAGE TEST: DC 300V 10ms;
INSULATION RESISTANCE: 10.0M OHM/MIN;
CONDUCTANCE RESISTANCE: 5.0 OHM/MAX.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

**RECOMMENDED
PANEL CUTOUT**

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY J.YOU	11/16/17		CATEGORY AUDIO/VIDEO PRODUCT DESCRIPTION CA USB-C PNL/USB-CM	
	CHECKED BY DFRISIELLO	11/16/17			
	APPROVED BY BGATES	11/16/17			
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	DWG. NO. U3A00057	REV. B
		SCALE: NONE	CAD FILE: U3A00057.SLDDRW	SHEET 1 OF 1	