


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
F	ECN 6881: UPD DRAWING FORMAT, PKG. AND DIMENSIONS.	6/12/13	D. DESJARDIN



F

NOTES:

MATERIAL:
 HOUSING: UL94V-0 RATED ABS, BLACK
 CONTACTS: PHOSPHOR BRONZE
 CONTACT FINISH: GOLD OVER NICKEL

ELECTRICAL:
 CURRENT RATING: 1.5 AMPS
 INSULATION RESISTANCE: 500MΩ (MIN)
 DC RESISTANCE: .1Ω (MAX)

PHYSICAL CHARACTERISTICS:
 INSERTION LIFE: 750 CYCLES
 TEMPERATURE RANGE : -40 °F TO 150 °F
 RATING: CATEGORY 5E
 WIRING: STRAIGHT THROUGH
 MAXIMUM PANEL THICKNESS: .07"

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
 ROHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY RON CARRICK	12/7/2001		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY C.MCCORMICK	12/7/2001	CATEGORY TELECOM/MODULAR	
	APPROVED BY DOUG PARHAM	12/7/2001	PRODUCT DESCRIPTION PNL CPLR 8X8 CAT5E KEYSTNE	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. UJ5T568
		SCALE: NONE	CAD FILE: UJ5T568.SLDDRW	SHEET 1 OF 1

F