

## 915 to 918 MHz Permanent Mount Mini Antenna Solder Post



### LCANRBD1062

#### Features

- 915 MHz to 918 MHz
- -0.5 dBi Gain
- Solder Post connector
- Embedded Through Hole
- VSWR 2:1
- Linear polarization

#### Applications

- LPWAN
- ISM
- LoRaWAN
- Sigfox
- Weightless-P
- WiFi HaLow
- Fixed and Mobile Devices

#### Description

The LCANRBD1062 is a high-quality single-band permanent mount mini antenna with -0.5 dBi nominal gain and has a frequency range of 915 MHz to 918 MHz. L-com's omnidirectional embedded through hole permanent mount mini antenna is 0.6 inches tall and 0.5 inches wide.

The LCANRBD1062 permanent mount mini antenna from L-com features a Solder Post connector with an input VSWR (voltage standing wave ratio) of 2:1.

L-com's linearly polarized antenna can operate at temperatures ranging from -40 °C to 60 °C. This single-band permanent mount mini antenna is offered with expert technical support, PDF datasheets, and CAD drawings with dimensions and specifications.

#### Configuration

Design	Embedded Through Hole
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Linear
Connector Type	Solder Post

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	915		918	MHz
Center Frequency		916		MHz
Input VSWR			2:1	
Impedance		50		Ohms
Gain		-0.5		dBi

#### Mechanical Specifications

Radome Material	TPEEL630
<b>Size</b>	
Length	0.6 in [15.24 mm]
Width	0.5 in [12.7 mm]
Height	0.5 in [12.7 mm]
Weight	0.2 lbs [90.72 g]

## 915 to 918 MHz Permanent Mount Mini Antenna Solder Post



### LCANRBD1062

#### Environmental Specifications

##### Temperature

Operating Range  
Storage Range

-20 to +60 deg C  
-30 to +70 deg C

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

#### Typical Radiation Pattern

#### Appendix

**Electrical Downtilt:** Angle in the antenna's elevation pattern in which the maximum gain occurs.

**Gain:** Antenna's average gain.

**Front to Back Ratio @ 180°±30°:** Average difference between the antenna's maximum gain and the maximum gain in the antenna's back lobe over  $\pm 30^\circ$  angles.

**Cross-polarization Ratio (dB):** Typical difference between the co-polarization and cross-polarization gain across the sector's 3 dB Beam Width.

Dedicated to serving the needs of the Wireless Internet Service Provider (WISP) market, KP Performance Antennas offers purpose built products that reliably perform in the field. KP Performance Antennas product line consists of Yagi, Grid, Omni, Dish and other style antennas that operate in the 900 MHz, 2.4 GHz, 3 GHz, and 5 GHz frequencies.

915 to 918 MHz Permanent Mount Mini Antenna Solder Post from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/915-918-mhz-perm-mnt-mini-antennas-solder-post-lcanrbd1062-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# LCANRBD1062 CAD Drawing

915 to 918 MHz Permanent Mount Mini Antenna Solder Post

