

136-174 MHz Telescopic Antenna, 2.5 dBi gain, TNC Male Connector, Vertical Polarization



## LCANRBD1031

### Features

- 136 MHz to 174 MHz, 2.5 dBi Gain
- TNC-Male connector
- Telescopic radiator
- Plug and play
- 50W power handling
- VSWR < 1.5:1
- Vertical polarization
- Black

### Applications

- PtP or PtMP applications
- Trunking for two-way radio comms
- VHF applications
- Public Safety / Emergency services
- Marine / Rail road communications
- P-25 applications exclusively supported
- Land mobile radio (LMR)
- Fixed and mobile services

### Description

The L-com LCANRBD1031 is a single band telescopic antenna that ships on the same day as ordered. Our vertical polarized antenna with 136 to 174 MHz frequency range has a TNC male connector. This antenna with a silver colored radome has an overall length of 17.2 in, a width of 0.500 in, and a weight of 0.22 lbs.

L-com's LCANRBD1031 is a single band antenna operating from 136 to 174 MHz with 2.5 dBi gain. The omni directional antenna has a maximum input VSWR of 1.5:1.

L-com has one of the largest in-stock collections of omni directional antennas with our wide selection of superior quality RF parts, that ship same day. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal single band rubber duck antenna as per your requirement.

### Configuration

Design	Rubber Duck
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	TNC Male

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	136		174	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		2.5		dBi
Input Power			50	Watts
.				

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[136-174 MHz Telescopic Antenna, 2.5 dBi gain, TNC Male Connector, Vertical Polarization LCANRBD1031](#)

136-174 MHz Telescopic Antenna, 2.5 dBi gain, TNC  
Male Connector, Vertical Polarization

**LCANRBD1031****Mechanical Specifications**

Radome Material	Silver
<b>Size</b>	
Length	17.2 in [436.88 mm]
Width	0.5 in [12.7 mm]
Height	0.5 in [12.7 mm]
Weight	0.22 lbs [99.79 g]

**Environmental Specifications**

<b>Temperature</b>	
Operating Range	-40 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

136-174 MHz Telescopic Antenna, 2.5 dBi gain, TNC Male Connector, Vertical Polarization from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

**L-com CAD Drawing**

