

Low Loss SMA Male to SMA Male Cable Assembly using LMR-200-FR Coax, 6 FT with Times Microwave Components



## LCCA30170-FT6

### Configuration


- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: LMR-200-FR

### Features

- Using Times Microwave Components
- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- FRPE Jacket
- Low Insertion Loss
- Bend Radius of 2 Inches

### Applications

- General Purpose
- Laboratory Use
- Antenna Installations
- Land Mobile Radio & Other Communication Systems
- Cellular & Wi-Fi Systems



### Description

L-com's LCCA30170-FT6 is a low loss SMA male to SMA male cable assembly using LMR-200-FR coax, 6 FT with Times Microwave components and ships same-day. The LMR-200-FR coax of this SMA cable uses the PE dielectric with a VoP of 83%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com SMA to SMA cable assembly has a male to male gender configuration with flexible LMR-200-FR series coax and operates to 5.8 GHz. The double shield of this SMA cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB. \*LMR<sup>TM</sup> is a trademark of Times Microwave Systems.

Custom versions of this SMA male to SMA male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30170-FT6 L-com Low Loss SMA Male to SMA Male Cable Assembly using LMR-200-FR Coax, 6 FT with Times Microwave Components data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Low Loss SMA Male to SMA Male Cable Assembly using LMR-200-FR Coax, 6 FT with Times Microwave Components



## LCCA30170-FT6

### Electrical Specifications

| Description                   | Minimum | Typical      | Maximum | Units                 |
|-------------------------------|---------|--------------|---------|-----------------------|
| Frequency Range               | DC      |              | 5.8     | GHz                   |
| Velocity of Propagation       |         | 83           |         | %                     |
| RF Shielding                  | 90      |              |         | dB                    |
| Group Delay                   |         | 1.22 [4]     |         | ns/ft [ns/m]          |
| Capacitance                   |         | 24.5 [80.38] |         | pF/ft [pF/m]          |
| Inductance                    |         | 0.061 [0.2]  |         | uH/ft [uH/m]          |
| DC Resistance Inner Conductor |         | 5.36 [17.59] |         | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor |         | 4.9 [16.08]  |         | Ohms/1000ft [Ohms/Km] |
| Jacket Spark                  |         |              | 3,000   | Vrms                  |

### Specifications by Frequency

| Description           | F1   | F2   | F3   | F4   | F5   | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency             | 0.25 | 0.5  | 1    | 2.5  | 5.8  | GHz   |
| Insertion Loss (Typ.) | 0.5  | 0.63 | 0.82 | 1.21 | 1.78 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length 72 in [182.88 cm]  
Diameter 0.312 in [7.92 mm]

#### Cable

Cable Type LMR-200-FR  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper  
Dielectric Type PE  
Number of Shields 2  
Shield Layer 1 Aluminum Tape  
Shield Layer 2 Tinned Copper Braid

Low Loss SMA Male to SMA Male Cable Assembly using LMR-200-FR Coax, 6 FT with Times Microwave Components



## LCCA30170-FT6

|                              |                        |
|------------------------------|------------------------|
| Jacket Material              | FRPE, Black            |
| Jacket Diameter              | 0.195 in [4.95 mm]     |
| One Time Minimum Bend Radius | 0.5 in [12.7 mm]       |
| Repeated Minimum Bend Radius | 2 in [50.8 mm]         |
| Bending Moment               | 2 lbs-ft [2.71 N-m]    |
| Flat Plate Crush             | 15 lbs/in [0.27 Kg/mm] |
| Tensile Strength             | 40 lbs [18.14 Kg]      |

### Connectors

| Description                        | Connector 1                | Connector 2                |
|------------------------------------|----------------------------|----------------------------|
| Type                               | SMA Male                   | SMA Male                   |
| Specification                      | MIL-STD-348                | MIL-STD-348                |
| Impedance                          | 50 Ohms                    | 50 Ohms                    |
| Contact Material and Plating       | Beryllium Copper, Gold     | Beryllium Copper, Gold     |
| Contact Plating Specification      | ASTM B488                  | ASTM B488                  |
| Dielectric Type                    | Teflon                     | Teflon                     |
| Body Material and Plating          | Passivated Stainless Steel | Passivated Stainless Steel |
| Body Plating Specification         | SAE-AMS-2700               | SAE-AMS-2700               |
| Coupling Nut Material and Plating  | Passivated Stainless Steel | Passivated Stainless Steel |
| Coupling Nut Plating Specification | SAE-AMS-2700               | SAE-AMS-2700               |
| Hex Size                           | 5/16 Inch                  | 5/16 Inch                  |

### Environmental Specifications

#### Temperature

|                 |                  |
|-----------------|------------------|
| Operating Range | -40 to +85 deg C |
| Storage Range   | -70 to +85 deg C |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:


Low Loss SMA Male to SMA Male Cable Assembly using LMR-200-FR Coax, 6 FT with Times Microwave Components



## LCCA30170-FT6

### How to Order

Part Number Configuration:



Example: LCCA30170-12 = 12 inches long cable  
LCCA30170-100cm = 100 cm long cable

Low Loss SMA Male to SMA Male Cable Assembly using LMR-200-FR Coax, 6 FT with Times Microwave Components from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Low Loss SMA Male to SMA Male Cable Assembly using LMR-200-FR Coax, 6 FT with Times Microwave Components

L-com CAD Drawing

