

## 2 Watt RF Load Up to 18 GHz With TNC Female Brass Body



### LCTR1172

#### Features

- DC to 18 GHz Frequency Range
- VSWR <1.2:1
- Max Power 2 Watt (CW)
- TNC Female Coaxial Interface

#### Applications

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communications

#### Description

L-com's LCTR1172 is an RF termination (also called RF load or dummy load) that operates from DC to 18 GHz and handles up to 2 Watt (CW). Our TNC termination/load has a female gender. LCTR1172 TNC load termination offers 1.2:1 VSWR max.

RF load / termination are indispensable components in many RF, microwave and millimeter wave systems where signal reflections from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. L-com offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
VSWR, Input			1.2:1	
Input Power (CW)			2	Watts
Derated linearly to 1W @ 165°C				
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Operating Voltage (AC)			500	Vrms

#### Mechanical Specifications

##### Size

Length	0.902 in [22.91 mm]
Width	0.433 in [11 mm]
Height	0.433 in [11 mm]
Weight	0.025 lbs [11.34 g]

##### Configuration

Connector	TNC Female
Mating Torque	4.1 to 6.1 in-lbs [0.46 to 0.69 Nm]

## 2 Watt RF Load Up to 18 GHz With TNC Female Brass Body



### LCTR1172

#### Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold over nickel
Insulation	Teflon	
Connector 1 Body	Stainless Steel	Passivated

#### Environmental Specifications

##### Temperature

Operating Range

-55 to +70 deg C

Humidity

MIL-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

#### Compliance Certifications (see product page for current document)

#### Plotted and Other Data

Notes:

2 Watt RF Load Up to 18 GHz With TNC Female Brass Body from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/2-watts-tnc-female-rf-load-18-ghz-lctr1172-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# LCTR1172 CAD Drawing

2 Watt RF Load Up to 18 GHz With TNC Female Brass Body

