

Pressure Sensor, compact, 1 MPa, 4-20mA, G1/4, 1.5m cable

PT211A-201DW Pressure Sensor



Features

- Advanced Microfused Silicon Strain Gauge
- Efficient lightning protection
- Strong RFI&EMI protection
- Advanced digital temperature compensation
- Wide working temperature range
- High accuracy, high frequency response
- Compact design
- Cost effective

Applications

- Industrial process control
- Automatic testing system
- Hydraulic and pneumatic systems
- Pump station and water treatment system
- Industrial machinery

Description

The PT211A-201DW from L-com is a gauge-style pressure sensor with a 1 MPa maximum pressure range. This pressure sensor has a 4-20 mA output with 1.5 meter cable electric connection. This 1 MPa sensor is powered by DC voltage ranging from 9 to 30 VDC. Our pressure sensor has an IP65 ingress protection rating. Make your online purchase right now to take advantage of our same-day shipping.

General Specifications

Application: Pressure Sensor

Pressure Type: Gauge

Electrical Connector: 1.5 meter cable

Process Connector: G1/4

Output Signal: 4-20 mA

Description	Minimum	Typical	Maximum	Unit
Pressure Range	0		1	Mpa
Accuracy		±0.5		% Full Scale
Compensated Temp Range	-10		70	deg C
Overpressure		300		% Full Scale
Destruction Pressure		500		% Full Scale
Long Term Stability		0.2		% Full Scale
Temperature Range	-40		85	deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
Pressure Sensor, compact, 1 MPa, 4-20mA, G1/4, 1.5m cable PT211A-201DW

Pressure Sensor, compact, 1 MPa, 4-20mA, G1/4, 1.5m cable



PT211A-201DW Pressure Sensor

Electrical Specifications

Description	Minimum	Typical	Maximum	Unit
Power Supply/Excitation Level	9	24	30	VDC

Material Specifications

Description	Material
Housing	SS (17-4PH)

Mechanical Specifications

RoHS Compliant Yes

Environmental Specifications

Temperature (Operating)	-40deg C to 85deg C
Temperature (Storage)	-40deg C to 125deg C
Shock	100 g
Ingress Protection	IP65


The Infinite Electronics portfolio includes coaxial cable assemblies, connectors, adapters and custom products, as well as our wireless product line which includes antennas, RF amplifiers, lightning and surge protectors, and NEMA rated enclosures.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.



PT211A-201DW CAD Drawing

Pressure Sensor, compact, 1 MPa, 4-20mA, G1/4, 1.5m cable

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/11/2023	KGLLEBOVA	THOUGHTON



ELECTRICAL CONNECTION



 L-com <i>an INFINITE® brand</i>		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES:	$X = \pm 2 [5]$ $.XX = \pm 0.05 [0.13]$ $XXX = \pm .005 [0.013]$	FRACTIONS $\pm 1/32$ ANGLES $\pm ^\circ$ CABLE LENGTH TOLERANCES	SCALE NONE SHEET 1 OF 1
		DESCRIPTION	
		Phone: 1.800.341.5266 978.682.6936 Website: www.L-com.com	
		PRESSURE SENSOR, COMPACT, 1 MPa, 4-20mA, G1/4, 1.5m CABLE	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UNDIMENTIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY		ITEM NO.	PT211A-201DW
SIZE A	CAGE CODE 43321	DRAWN BY KGLEBOVA	REV A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.