

HyperLink Brand Outdoor Passive Gigabit Power-Over-Ethernet (PoE) Midspan / Injector with Integral Hi-Power CAT6 Surge Protection - Model: BT-CAT6-P1-HPW

Applications & Features

Applications:

- Wireless LAN Access Points and Bridges
- WAN millimeter radios
- High definition IP Surveillance Cameras
- Wired gigabit PoE switches

Features:

- IEEE 802.3af and 802.3at compatibility
- Surge Protection on all lines
- User configurable power feed and resettable PTC fuse
- GR-1089 Intra-Building rated
- Up to 60 volts DC or AC power



Description

The BT-CAT6-P1-HPW Outdoor Single-Port Gigabit CAT6 Midspan/Injector is a commercial grade Power-over-Ethernet device that provides DC or AC power for one 10/100/1000 Base-T Power-over-Ethernet, PoE equipped Network Appliance device. The unit uses Gigabit transformers on all four data pairs in contrast to cheaper designs that only use transformers for two pairs. It is compatible with devices that support the IEEE 802.3af and 802.3at standard PoE power feed using Mode B (Pins 4/5 and 7/8). The unit can also be user configured using internal jumpers to supply power up all four data pairs simultaneously (Pins 1/2, 3/6, 4/5 and 7/8). The majority of IEEE 802.3af and 802.3at Network Appliances can pull power off all four data pairs simultaneously. This allows higher power to be fed up the cable and cuts resistive power losses in the cable by half. The unit supports both positive and negative DC as well as AC power up to 60 volts. Power-over-Ethernet eliminates the need for an AC outlet at each Network Appliance location. An integral PTC fuse cuts power in case of a short. The PTC fuse auto resets after the short is removed.

Integral High Power Surge Protection

The BT-CAT6-P1-HPW features integral surge protection for the data and power feeds for networks. The BT-CAT6-P1-HPW has been designed to meet the GR-1089 Intra-Building surge protection requirements for Ethernet lines. The design provides protection for both common and differential mode surges. The design utilizes three-pole differential Gas Tubes. The tubes feature ultra-low Line to Line and Line to Ground capacitance to minimize distortion of high-speed signals.



The BT-CAT6-P1-HPW features shielded RJ45 jacks which helps reduce the effects of EMI interference. A ground lug and terminal is provided directly on the injector providing superior grounding. The compact weather resistant housing features a lockable hinged cover and mounting holes are provided on the rear of the enclosure for mounting. The two cable grommets may be adjusted to cable size and are removable.

This unit is available individually or as in a kit version featuring either a 48VDC @ 48 Watt or a 48VDC @ 70 Watt power supply.

Note: Power supplies are for use either indoors or in weather resistant enclosures.



Specifications

Electrical Specifications

Max Voltage	60 Volts AC/DC
Max Current	1.5 A
Power Connector	Standard 2.5mm Coaxial DC Power Jack (2.5mm x 5.5mm x 10mm)
Ethernet Connectors	(2) Shielded RJ45 Jacks
Data Lines	Pair 1: Pins 1 and 2 Pair 2: Pins 3 and 6 Pair 3: Pins 4 and 5 Pair 4: Pins 7 and 8
Power Lines (Default)	+/- VDC: Pins 4 & 5 +/- VDC: Pins 7 & 8
Power Lines (Jumper Configured)	+/- VDC: Pins 1 & 2 +/- VDC: Pins 3 & 6
Gas Tube Voltage	+/- 90 Volts

Mechanical Specifications

Enclosure Material	Gray Polycarbonate
Ground Lug	12 AWG Max.
Operating Temp - Injector	-40° C to +70° C
Weight	.40 lbs. (.18 kg)
Dimensions	4.75 x 4.06 x 2.81 (in) 120.6 x 103.1 x 71.3 (mm)
RoHS Compliant	Yes

