

7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For LMR-600, LMR-600-DB, LMR-600-FR, and 600-Series Cable



#### EZ-600-716M-X-LC



# Times Microwave Systems Connector Specification Configuration

- 7/16 DIN Male Connector
- 50 Ohms
- · Straight Body Geometry

- LMR-600, LMR-600-DB, LMR-600-FR, 600-Series Interface Type
- Crimp/Non-Solder Contact Attachment
- 1 1/4 in Hex

#### **Features**

- · Designed to industry standard interface dimensions
- · Quality body materials and plating

#### **Applications**

- · RF Boxes and components
- · RF Test systems

- Crimp/Non-Solder Contact attachment
- Operates to 3 GHz
- General Purpose RF Interconnect
- · Laboratory applications

#### Description

L-com's 7/16 DIN Male connector for LMR-600, LMR-600-DB, LMR-600-FR and 600-Series coax uses a Crimp/Non-Solder Contact attachment method. This 7/16 DIN connector is one of the many RF coaxial connectors in L-com's product line up and like all our products, they will ship the same day. Our 7/16 DIN Male connector operates up to a maximum frequency of 3 GHz.

The specifications and a basic dimensional drawing for EZ-600-716M-X-LC Male 7/16 DIN connector can be found in this datasheet PDF. L-com's portfolio of RF and microwave connectors allows users to choose from a large number of options when building assemblies to fit their RF interconnect needs. RF cables can be created to fulfill many interconnect applications ranging from In the Box hookup, test equipment connectivity or as part of a system installation. In addition to an offering of RF connectors and coaxial cable L-com offers both standard and custom cable assemblies to fit a customer's specific needs.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units	
Frequency Range	DC		3	GHz	
VSWR			1.15:1		
Return Loss			0.05	dB	
Operating Voltage (AC)			2,500	Vrms	

#### **Mechanical Specifications**

Width/Dia.	1.25in	[31.75mm]
Weight	0.298lbs	[135.17g]
Mating Torque	221in-lbs	[24.97Nm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For LMR-600, LMR-600-DB, LMR-600-FR, and 600-Series Cable EZ-600-716M-X-LC



7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For LMR-600, LMR-600-DB, LMR-600-FR, and 600-Series Cable



#### EZ-600-716M-X-LC



#### **Material Specifications**

Description	Material	Plating
Contact	Copper	Silver
		196µ in. minimum
Insulation	PTFE	
Outer Conductor	Brass	Tri-Metal
		78µin. minimum
Body	Brass	Tri-Metal
		78μ in. minimum
Coupling Nut	Brass	Nickel
		196µ in. minimum

## **Environmental Specifications**

**Temperature** 

Operating Range

-55°C to +155°C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For LMR-600, LMR-600-DB, LMR-600-FR, and 600-Series Cable from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For LMR-600, LMR-600-DB, LMR-600-FR, and 600-Series Cable EZ-600-716M-X-LC

URL: https://www.l-com.com/7-16-din-male-connector-crimp-non-solder-contact-attachment-lmr-600-lmr-600-db-lmr-600-fr-600-series-cable-ez-600-716m-x-lc-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

### **L-com CAD Drawing**

