


4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-10M



FCA-4M4LCUSTURK2-10

Features

- 4X LC UPC to 4X ST UPC
- Indoor multimode OM4
- Riser (OFNR) rated cable
- 4.5mm with tight-buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for ceilings and riser areas

Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

Description

The L-com FCA-4M4LCUSTURK2-10 is a fiber optic breakout cable assembly that is equipped with 4-fiber LC/UPC to ST/UPC connectors. This distribution cable assembly comes with a multimode OM4 fiber that supports 10 Gb Ethernet up to 550 meters and 40G/100G Ethernet up to 150 meters and a bandwidth of 4700 MHz.km that delivers low attenuation and high-speed performance for mission-critical applications. The aqua blue fiber optic cable has an OFNR-rated PVC jacket and a length of 10 meters.

Our fiber optic breakout cable is a robust and versatile fiber optic assembly designed for high-performance data transmission in various environments. L-com's OM4 fiber optic breakout assembly is designed for hyperscale data centers and telecom backbones and ensures seamless network connectivity with minimal signal loss. With an operating temperature range of -20 to 70 degrees C, this cable assembly provides reliable performance across diverse conditions.

This fiber optic cable from L-com is suitable for applications such as data centers, passive optical networks (PON), local area networks (LAN), enterprise networking, storage and cloud based services, AI data storage and communications, headend termination to a fiber backbone, and terminations of data center fiber rack system. Our breakout cable comes with a cable diameter of 4.5 mm and has an insertion loss of 0.3 dB. Additional dimensions, specifications, and CAD drawings for this 4-fiber cable assembly can be found on its downloadable PDF datasheet.

L-com has one of the largest in-stock selections of LC/UPC to ST/UPC fiber optic breakout cords for international and domestic orders. We are committed to delivering excellent service to support our customers in maintaining the continuity and reliability of their networks. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal OM4 multimode fiber optic cable that meets your requirements.


Configuration

Function	Breakout
Cable Type	Base-4 Multimode
Mode	Multimode
Mode Class	OM4
Fiber Diameter	50/125 µm
Connection 1 Type	LC
Connection 1 Polish	UPC
Connection 2 Type	ST
Connection 2 Polish	UPC
Cable Color	Aqua Blue

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Return Loss - LC, ST, SC, FC	30			dB

4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution
Cable, 4.5mm Riser, 2.0mm breakout, Aqua-10M



FCA-4M4LCUSTURK2-10

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Insertion Loss - LC, ST, SC, FC			0.3	dB

Mechanical Specifications

Cable Assembly

Length	10 m [393.70 in]
Width/Diameter	4.5 mm
Weight	92.53 g [0.204 lbs]

Cable

Cable Type	Breakout
Static Bend Radius	34 mm
Dynamic Bend Radius	67 mm
Max Crush Resistance, Short Term (N/100mm)	1,000
Max Crush Resistance, Long Term (N/100mm)	300

Connectors

Description	Connector 1	Connector 2
Type	LC	ST
Connector Polish	UPC	UPC

Environmental Specifications


Operating Range Temperature	-20 to +70 deg C
Storage Range Temperature	-40 to +70 deg C
Ingress Protection (IP) Rating	Non-Rated

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-10M



FCA-4M4LCUSTURK2-10

Typical Performance Data

How to Order

Part Number Configuration:

FCA-4M4LCUSTURK2

-XX

UU

Unit of Measure:

F = Feet

<blank> = Meters

Lengths

Base Number

Example: FCA-4M4LCUSTURK2-12 = 12 meters long cable
FCA-4M4LCUSTURK2-10F = 10 feet long cable

4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-10M from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/4-fiber-lc-upc-st-upc-om4-multimode-distribution-cable-4.5mm-riser-2.0mm-breakout-aqua-10m-fca-4m4l-custurk2-10-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

FCA-4M4LCUSTURK2-10 CAD Drawing

4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm Riser, 2.0mm breakout, Aqua-10M

