
# 6-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M



## FCA-6M1SCUSTURK2-5

### Features

- 6X SC UPC to 6X ST UPC
- Indoor multimode OM1
- Riser (OFNR) rated cable
- 5.0mm with tight buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for ceilings and riser areas

### Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

### Description

L-com's FCA-6M1SCUSTURK2-5 fiber optic distribution cable is designed to support dependable multimode fiber connectivity in indoor network environments. This cable assembly features a 6-fiber SC UPC to ST UPC configuration using OM1 multimode fiber with a 62.5/125 µm core size. Our fiber optic cable has a breakout design that supports organized fiber distribution and is commonly used in data centers, enterprise networks, and LAN applications where multi-fiber routing and signal consistency are required. This 6-fiber multimode breakout cable is constructed with a 5.0 mm overall diameter orange riser (OFNR)-rated PVC jacket to meet indoor fire safety requirements. Each breakout fiber measures 2.0 mm and follows TIA-598 color coding for simplified identification and termination, with a 0.5 m breakout length.

Our fiber optic distribution cable features tight-buffered fiber construction with aramid yarn that provides mechanical durability, while controlled one-time and repeated bend radius values of 1.969 in and 3.937 in respectively help maintain optical performance during installation and routing. The cable also offers short-term and long-term crush resistance values of 1000 N/100 mm and 300 N/100 mm to support robust indoor deployment. The FCA-6M1SCUSTURK2-5 OM1 fiber optic cable assembly uses SC UPC to ST UPC connectors to support low insertion loss and stable return loss performance, with a maximum insertion loss of 0.30 dB and a minimum return loss of 30 dB.

This 5 m OM1 multimode fiber assembly is suitable for 100 Mb Ethernet applications and supports 10 Gb Ethernet transmission over short distances. Typical deployment environments include data centers, enterprise networks, LAN systems, Passive Optical Networks (PON), storage and cloud-based services, AI data storage and communications, headend termination to a fiber backbone, and terminations of data center fiber rack systems. This cable operates from -20°C to 70°C and is designed for indoor wall, ceiling, conduit, and rack-to-rack installations, with no ingress protection rating.


L-com offers one of the largest in-stock selections of multimode distribution cables, with same-day shipment available for domestic and international orders. Make your online purchase today to take advantage of our same-day shipping. Our expert technical support and knowledgeable sales team are ready to assist you in selecting the 6-fiber SC UPC to ST UPC OM1 multimode distribution cable that meets your needs.

### Configuration

| | |
|---|---|
| Function | Breakout |
| Cable Type | Base-6 Multimode |
| Mode | Multimode |
| Mode Class | OM1 |
| Fiber Diameter | 62.5/125 um |
| Connection 1 Type | SC |
| Connection 1 Polish | UPC |
| Connection 2 Type | ST |
| Connection 2 Polish | UPC |
| Cable Color | Orange |


© 2026 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.

# 6-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M



## FCA-6M1SCUSTURK2-5

### Optical Specifications

| Description | Minimum | Typical | Maximum | Units |
|---|---|---|---|---|
| Return Loss - LC, ST, SC, FC | 30 | | | dB |
| Insertion Loss - LC, ST, SC, FC | | | 0.3 | dB |

### Mechanical Specifications

**Cable Assembly**

| | |
|---|---|
| Length | 5 m [196.85 in] |
| Width/Diameter | 5 mm |
| Weight | 97.07 g [0.214 lbs] |

**Cable**

| | |
|---|---|
| Cable Type | Breakout |
| Static Bend Radius | 50 mm |
| Dynamic Bend Radius | 100 mm |
| Max Crush Resistance, Short Term (N/100mm) | 1,000 |
| Max Crush Resistance, Long Term (N/100mm) | 300 |

### Connectors

| Description | Connector 1 | Connector 2 |
|---|---|---|
| Type | SC | ST |
| Connector Polish | UPC | UPC |

### Environmental Specifications

| | |
|---|---|
| Operating Range Temperature | -20 to +70 deg C |
| Storage Range Temperature | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated |

### Compliance Certifications (see product page for current document)


### Plotted and Other Data

Notes:



© 2026 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.

# 6-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M



## FCA-6M1SCUSTURK2-5

### Typical Performance Data

### How to Order

Part Number Configuration: **FCA-6M1SCUSTURK2** **-XX** **UU**

- UU — Unit of Measure:
  F = Feet
  <blank> = Meters
- -XX — Lengths
- FCA-6M1SCUSTURK2 — Base Number

Example: FCA-6M1SCUSTURK2-12 = 12 meters long cable
FCA-6M1SCUSTURK2-10F = 10 feet long cable

6-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.


URL: https://www.l-com.com/6-fiber-sc-upc-st-upc-om1-multimode-distribution-cable-5.0mm-riser-2.0mm-breakout-orange-5m-fca-6m1s-custurk2-5-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.


© 2026 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.

# FCA-6M1SCUSTURK2-5 CAD Drawing

6-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M






© 2025 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.