


## 8-Fiber SC UPC to SC UPC, OM3 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Aqua-30M



### FCA-8M3SCUSCUPK2-30

#### Features

- 8X SC UPC to 8X SC UPC
- Indoor multimode OM3
- Plenum (OFNP) rated cable
- 5.6mm with tight buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for wall, ceiling, conduits, and between buildings

#### Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

#### Description

L-com's FCA-8M3SCUSCUPK2-30 fiber optic distribution cable is engineered to provide reliable multimode fiber connectivity for indoor network environments. This cable assembly features an 8-fiber SC UPC to SC UPC configuration, using OM3 multimode fiber with a 50/125  $\mu\text{m}$  core size. Designed with a breakout structure, it ensures organized fiber distribution, making it an ideal choice for data centers, enterprise networks, and LAN applications where multi-fiber routing and consistent signal performance are critical. The 8-fiber multimode breakout cable comes with a 5.6 mm overall diameter aqua blue plenum (OFNP)-rated PVC jacket, meeting indoor fire safety standards. Each breakout fiber measures 2.0 mm and follows TIA-598 color coding for easy identification and termination, with a 0.5 m breakout length.

This fiber optic distribution cable is constructed with tight-buffered fiber and reinforced with aramid yarn, providing excellent mechanical durability. The cable also features controlled bend radii, with a one-time bend radius of 1.654 inches and a repeated bend radius of 3.307 inches, ensuring optimal optical performance during installation and routing. The cable offers crush resistance values of 1000 N/100 mm (short-term) and 300 N/100 mm (long-term), making it highly suitable for robust indoor deployments.


The FCA-8M3SCUSCUPK2-30 OM3 30-meter fiber optic assembly uses SC UPC to SC UPC connectors, which ensure low insertion loss and stable return loss performance. The maximum insertion loss is 0.30 dB, with a minimum return loss of 30 dB. This OM3 multimode fiber assembly is perfect for applications such as Passive Optical Networks (PON), storage and cloud-based services, AI data storage and communications, headend termination to a fiber backbone, and data center fiber rack systems. With an operating temperature range of 0 °C to 60 °C, this cable is designed for installations on walls, ceilings, conduits, and for use between buildings. It does not have an ingress protection rating.

L-com offers one of the most extensive in-stock selections of multimode distribution cables, with same-day shipping available for both domestic and international orders. Order today to take advantage of same-day shipping, and our expert technical support and knowledgeable sales team are available to help you select the 8-fiber SC UPC to SC UPC OM3 multimode distribution cable that fits your needs.

#### Configuration

|                     |                      |
|---------------------|----------------------|
| Function            | Breakout             |
| Cable Type          | Base-8 Multimode     |
| Mode                | Multimode            |
| Mode Class          | OM3                  |
| Fiber Diameter      | 50/125 $\mu\text{m}$ |
| Connection 1 Type   | SC                   |
| Connection 1 Polish | UPC                  |
| Connection 2 Type   | SC                   |
| Connection 2 Polish | UPC                  |
| Cable Color         | Aqua Blue            |

8-Fiber SC UPC to SC UPC, OM3 Multimode Distribution  
Cable, 5.6mm Plenum, 2.0mm breakout, Aqua-30M



## FCA-8M3SCUSCUPK2-30

### Optical Specifications

| Description                     | Minimum | Typical | Maximum | Units |
|---------------------------------|---------|---------|---------|-------|
| Return Loss - LC, ST, SC, FC    | 30      |         |         | dB    |
| Insertion Loss - LC, ST, SC, FC |         |         | 0.3     | dB    |

### Mechanical Specifications

#### Cable Assembly

|                |                      |
|----------------|----------------------|
| Length         | 30 m [1181.10 in]    |
| Width/Diameter | 5.6 mm               |
| Weight         | 270.34 g [0.596 lbs] |

#### Cable

|                                            |          |
|--------------------------------------------|----------|
| Cable Type                                 | Breakout |
| Static Bend Radius                         | 42 mm    |
| Dynamic Bend Radius                        | 84 mm    |
| Max Crush Resistance, Short Term (N/100mm) | 1,000    |
| Max Crush Resistance, Long Term (N/100mm)  | 300      |

### Connectors

| Description      | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type             | SC          | SC          |
| Connector Polish | UPC         | UPC         |

### Environmental Specifications


|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | 0 to +60 deg C   |
| Storage Range Temperature      | -20 to +60 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

8-Fiber SC UPC to SC UPC, OM3 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Aqua-30M



## FCA-8M3SCUSCUPK2-30

### Typical Performance Data

### How to Order

Part Number Configuration:

**FCA-8M3SCUSCUPK2**

**-XX**

**UU**

Unit of Measure:

F = Feet

<blank> = Meters

Lengths

Base Number

Example: FCA-8M3SCUSCUPK2-12 = 12 meters long cable  
FCA-8M3SCUSCUPK2-10F = 10 feet long cable


8-Fiber SC UPC to SC UPC, OM3 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Aqua-30M from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/8-fiber-sc-upc-sc-upc-om3-multimode-distribution-cable-5.6mm-plenum-2.0mm-breakout-aqua-30m-fca-8m3s-cuscupk2-30>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

FCA-8M3SCUSCUPK2-30 CAD Drawing

8-Fiber SC UPC to SC UPC, OM3 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Aqua-30M



- NOTES:
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.
  - CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS IN INCHES DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:

X = ±2 [5] FRACTIONS  
XX = ±0.02 [0.5] ± 1/32  
XXX = ±0.05 [1.3] ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤12 [305] = ±1 [25] / 0  
>12 [305] ≤ 60 [1524] = ±2 [51] / 0  
>60 [1524] ≤ 120 [3048] = ±4 [102] / 0  
>120 [3048] ≤ 300 [7620] = ±6 [152] / 0  
>300 [7620] = ±5% / 0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS IN INCHES DIMENSIONS IN [ ] ARE MILLIMETERS  
MAY VARY  
COLORS MAY VARY



an INFINITE brand

Website: [www.L-com.com](http://www.L-com.com)

Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE NONE

SHEET 1 OF 1

DESCRIPTION

8-FIBER SC UPC TO SC UPC, OM3 MULTIMODE DISTRIBUTION CABLE, 5.6mm PLENUM, 2.0mm BREAKOUT, AQUA

|      |           |          |                  |
|------|-----------|----------|------------------|
| SIZE | CAGE CODE | DRAWN BY | ITEM NO.         |
| A    | 43321     | DMAY     | FCA-8M3SCUSCUPK2 |

|     |   |
|-----|---|
| REV | A |
|-----|---|