

## 6-Fiber LC UPC to LC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M



### FCA-6M1LCULCURK2-5

#### Features

- 6X LC UPC to 6X LC UPC
- Indoor multimode OM1
- Riser (OFNR) rated cable
- 5.0mm with tight buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for ceilings and riser areas

#### Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

#### Description

L-com's FCA-6M1LCULCURK2-5 fiber optic distribution cable is designed to support dependable multimode fiber connectivity in indoor network environments. This cable assembly features a 6-fiber LC UPC to LC UPC configuration, using OM1 multimode fiber with a 62.5/125  $\mu$ m core size. Our fiber optic cable has a breakout design that supports organized fiber distribution and is commonly used in data centers, enterprise networks, and LAN applications, where multi-fiber routing and signal consistency are required. This 6-fiber multimode breakout cable is constructed with a 5.0 mm overall diameter orange riser (OFNR)-rated PVC jacket to meet indoor fire safety requirements. Each breakout fiber measures 2.0 mm and follows TIA-598 color coding for simplified identification and termination, with a 0.5 m breakout length.

Our fiber optic distribution cable features tight-buffered fiber construction with aramid yarn that provides mechanical durability, while controlled one-time and repeated bend radius values of 1.969 in and 3.937 in, respectively, help maintain optical performance during installation and routing. The cable also offers short-term and long-term crush resistance values of 1000 N/100 mm and 300 N/100 mm, respectively, to support robust indoor deployment.


The FCA-6M1LCULCURK2-5 OM1 5-meter fiber optic cable assembly uses LC UPC to LC UPC connectors to support low insertion loss and stable return loss performance, with a maximum insertion loss of 0.30 dB and a minimum return loss of 30 dB. This OM1 multimode fiber assembly is suitable for Passive Optical Networks (PON), storage and cloud-based services, AI data storage and communications, headend termination to a fiber backbone, and termination of data center fiber rack systems. This cable operates from -20°C to 70°C and is designed for indoor wall, ceiling, conduit, and rack-to-rack installations, with no ingress protection rating.

L-com offers one of the largest in-stock selections of multimode distribution cables, with same-day shipment available for domestic and international orders. Make your online purchase today to take advantage of our same-day shipping. Our expert technical support and knowledgeable sales team are ready to assist you in selecting the 6-fiber LC UPC to LC UPC OM1 multimode distribution cable that meets your needs.

#### Configuration

|                     |                  |
|---------------------|------------------|
| Function            | Breakout         |
| Cable Type          | Base-6 Multimode |
| Mode                | Multimode        |
| Mode Class          | OM1              |
| Fiber Diameter      | 62.5/125 $\mu$ m |
| Connection 1 Type   | LC               |
| Connection 1 Polish | UPC              |
| Connection 2 Type   | LC               |
| Connection 2 Polish | UPC              |
| Cable Color         | Orange           |

6-Fiber LC UPC to LC UPC, OM1 Multimode Distribution  
Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M



## FCA-6M1LCULCURK2-5

### Optical Specifications

| Description                     | Minimum | Typical | Maximum | Units |
|---------------------------------|---------|---------|---------|-------|
| Return Loss - LC, ST, SC, FC    | 30      |         |         | dB    |
| Insertion Loss - LC, ST, SC, FC |         |         | 0.3     | dB    |

### Mechanical Specifications

#### Cable Assembly

|                |                    |
|----------------|--------------------|
| Length         | 5 m [196.85 in]    |
| Width/Diameter | 5 mm               |
| Weight         | 75.3 g [0.166 lbs] |

#### Cable

|                                            |          |
|--------------------------------------------|----------|
| Cable Type                                 | Breakout |
| Static Bend Radius                         | 50 mm    |
| Dynamic Bend Radius                        | 100 mm   |
| Max Crush Resistance, Short Term (N/100mm) | 1,000    |
| Max Crush Resistance, Long Term (N/100mm)  | 300      |

### Connectors

| Description      | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type             | LC          | LC          |
| Connector Polish | UPC         | UPC         |

### Environmental Specifications

|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -20 to +70 deg C |
| Storage Range Temperature      | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

6-Fiber LC UPC to LC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M



## FCA-6M1LCULCURK2-5

### Typical Performance Data

### How to Order

Part Number Configuration:

**FCA-6M1LCULCURK2**

**-XX**

**UU**

Unit of Measure:

F = Feet

<blank> = Meters

Lengths

Base Number

Example: FCA-6M1LCULCURK2-12 = 12 meters long cable  
FCA-6M1LCULCURK2-10F = 10 feet long cable


6-Fiber LC UPC to LC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/6-fiber-lc-upc-lc-upc-om1-multimode-distribution-cable-5.0mm-riser-2.0mm-breakout-orange-5m-fca-6m1lcul-curk2-5-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

FCA-6M1LCULCURK2-5 CAD Drawing

6-Fiber LC UPC to LC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-5M



UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN INCHES. DIMENSIONS IN [ ] ARE MILLIMETERS.

TOLERANCES:  
X = ±.2 [5]  
.XX = ±.02 [0.5]  
.XXX = ±.005 [0.13]  
FRACTIONS: ± 1/32  
ANGLES: ± 1°

CABLE LENGTH TOLERANCES:  
≤ 12 [305] ±.60 [15.24] = ±.2 [5.1] / -0  
> 12 [305] ≤ 60 [1524] = ±.4 [10.2] / -0  
> 60 [1524] ≤ 120 [3048] = ±.4 [10.2] / -0  
> 120 [3048] ≤ 300 [7620] = ±.4 [10.2] / -0  
> 300 [7620] = ±.5% L / 0

ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS SHALL BE INDIVIDUALLY PACKAGED. UNLESS OTHERWISE SPECIFIED, DIMENSIONS SHALL BE INDIVIDUALLY PACKAGED. UNLESS OTHERWISE SPECIFIED, DIMENSIONS SHALL BE INDIVIDUALLY PACKAGED. UNLESS OTHERWISE SPECIFIED, DIMENSIONS SHALL BE INDIVIDUALLY PACKAGED.

**L-com**  
an INFINITE brand  
Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5  
SCALE: NONE  
SHEET: 1 OF 1

DESCRIPTION  
6-FIBER LC UPC TO LC UPC, OM1 MULTIMODE DISTRIBUTION CABLE, 5.0mm RISER, 2.0mm BREAKOUT, ORANGE

SIZE: A  
CAGE CODE: 43321  
DRAWN BY: TDUFRENE  
ITEM NO.: FCA-6M1LCULCURK2

REV: A

- NOTES:
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.
  - CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.