

HG10382DU-GPS

Features

- Duplexer (VHF/UHF 108-174MHz/380-870MHz) with integral N- RG-58/U NMO mount (1 ea.) Type (m) Connectors (3 ea.)
- Low Loss HG-GPSNMO58-SMA NMO Combination mount with
 RG-58/U Feed Vable (1 ea.) integrated GPS antenna (1 ea.)

Applications

- Service Vehicles
- Public Safety

• Field Tunable Antennas (2 ea.)

- Description
- Combined with a GPS antenna, this VHF/UHF duplexed mobile antenna kit is ideally suited for multipoint mobile applications including service vehicles, public transportation, public safety, mining and construction vehicles, as well numerous other commercial and industrial applications where mobility and wide coverage is desired. The antenna kit features a VHF/UHF duplexer, a pair of field tunable antennas, and a GPS antenna. This gives users the flexibility to operate radio transceivers in any VHF and UHF band with optimum performance. The kit allows the user to upgrade/switch to any NMO-type antenna.

Configuration

1

Design	Duplexed
Application Band	VHF/UHF
Band Type	Dual
Cable Length	204 in [518.16 cm]
Connector Type	NMO Mount
Interface 2	Ν

Duplexer Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range (VHF)	100		180	MHz
Frequency Range (UHF)	380		870	MHz
Input VSWR (All Ports)			1.6:1	
Impedance		50		Ohms
Isolation (VHF↔UHF-870)	50			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Dual Band Duplexed Antenna Kit with GPS 108-174 380-870 MHz NMO Mount/N Type Connectors HG10382DU-GPS



HG10382DU-GPS REV | © 2019 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.



· Public Transportation Mining & Construction

cuance	
ation (VHF↔UHF-870)	50
Electrical Specification Notes:	

Electrical specifications data applies to Duplexer





HG10382DU-GPS

GPS Antenna Electrical Specifications

Min	Тур	Max	Max
	1575.42 ± 3		MHz
	30		dB
		2:1	
	50		Ω
3		5.5	V
6		20	mA
	SAW		
35			dB
45			dB
	10		W
	3 6 35	1575.42 ± 3 30 50 3 6 SAW 35 45	1575.42 ± 3 30 2:1 50 3 5.5 6 20 SAW 35 45

GPS Antenna Passive Element Specifications

Description	Min	Тур	Max	Max
Center Frequency		1575.42		MHz
Antenna VSWR			1.5:1	
Impedance		50		Ω
Polarization		RHCP		

Antenna Efficiency

Frequency (MHz)	704	960	1575	1710	2170
Peak Gain (dBi)	2	1	2	4	4
Efficiency (%)	56	51	48	74	71

HG10382DU-GPS REV | © 2019 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.





HG10382DU-GPS

Field Tunable Antenna Electrical Specifications

Description	Min	Тур	Max	Max
Frequency Range	108		870	MHz
VSWR (Field Tunable)			1.6:1	
Impedance		50		Ω
Gain		2		dBi
Power Rating		100		W
Polarization		Linear, Vertical		
E-Plane		50		Degrees
H-Plane		Omnidirectional		
Ground Plane		Required		

Field Tunable Antenna Mechanical Specifications

Specifications by Band

Band 1	Band 2	Band 3	Band 4	Band 5	Units
100-180	380-520	746-870			MHz
0.2	0.3	0.5			dB
150	100	75			Watts
	100-180 0.2	100-180 380-520 0.2 0.3	100-180 380-520 746-870 0.2 0.3 0.5	100-180 380-520 746-870 0.2 0.3 0.5	100-180 380-520 746-870 0.2 0.3 0.5

Duplexer Mechanical Specifications

HG10382DU-GPS REV | © 2019 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.



HG10382DU-GPS



Duplexer Connectors Size Length Width Height Ν

3.27 in [83.06 mm] 2.1 in [53.34 mm] 1.1 in [27.94 mm]



HG10382DU-GPS



Installation Instructions

Parts (Figure 1): Verify all parts are included. Reference items in Figure 1:

- 1. (1 ea.) Multi-Band Duplexer
- 2. (2 ea.) Z-Nut[™] Field Tunable ¼ Wave Antenna
- 3. (3 ea.) Type N Connectors, RG-58/U & 195 Type
- 4. (1 ea.) HG-GPSNMO58-SMA NMO/GPS Combination Cable Mount
- 5. (1 ea.) 195 Low Loss NMO Cable Mount
- 6. (1 ea.) RG-58/U Feed Cable, 17 ft. (5.1m) length

Tools/Materials Required:


- Drill and Hole Punch, ¼" (19.05mm) Diameter NMO Cable Mount Installation
- #8 Self Tapping or Machine Screws (2 ea.) Duplexer Installation
- Cable Stripping Tools for RG-58/U & 195 type cable Connector Installations
 - Coaxial Connector (sold separately) for attaching Feed Cable (RG-58/U) to radio transceiver

Pre-Installation Checklist and Tips:

- Caution: Verify radio output power does not exceed rated power for each band of the duplexer:
 - VHF & 150W Max: (100-180 MHz) UHF & 100W, max: (380-520 MHz) 700/800 MHz & 75W, max: (746-870 MHz)
- Locate a suitable mounting location for the Duplexer providing the shortest cable lengths for installing both antennas.
 <u>Important:</u> Duplexer intended for interior or environmentally protected installation only. Do not install with direct
- exposure to outdoor environment.
 - Follow all instructions provided with each NMO Cable Mount and Field Tunable Antenna to be installed.
- Best Performance Recommendations:
 - > Minimize all cable lengths during installation to reduce unnecessary cable insertion loss.
 - Feed the UHF of 700/800 MHz Antenna using the 195 Low Loss NMO Cable Mount.
 - Separate antennas by largest distance possible to prevent VSWR mismatch or radiated obstruction. (<u>Note:</u> Duplexer provides >50 dB isolation between VHF and UHF/700-800 MHz antenna ports, maximizing cross-talk rejection.)

Installation:

- 1. Refer to figure 1 for antenna/duplexer system configuration.
- 2. Install Duplexer to a suitable mounting surface using #8 screws. Mounting Hole spacing: 2-15/16" (74.6mm).
- 3. Install NMO cable mount and NMO/GPS cable mount for each antenna according to the individual instructions.
- 4. Verify antenna cable routing. Cut excess cable. Strip ends of the NMO cable mounts according to the N Type Connector instructions provided with the connectors. Attach N Type connectors to the cables. Crimp and verify operation.
- Repeat Step 4 for <u>one end only</u> of RG-58/U Feed Cable. Attach radio transceiver connector (sold separately) to the opposite end of the RG-58/U Feed Cable.
- 6. Install and tune antennas according to the individual antenna instructions provide. Verify operation.
- 7. Attach GPS connector to GPS receiver. Attach all remaining connections according to the system diagram in Figure 1.
- 8. Verify radio transceiver performance for all required operating bands or channels.







HG10382DU-GPS




Installation Instructions FIELD TUNABLE "X"-NUT™ ANTENNA & REPLACEMENT WHIP 108-960 MHZ

PLEASE READ INSTRUCTIONS CAREFULLY BEFORE INSTALLING AND TUNING ANTENNA

- 1. <u>IMPORTAND:</u> When Installing Replacement Whips, press Rubber Friction Washer is secure and pressed completely flat around the base of the threaded stud. Attach Replacement Whip to the NMO Antenna Base by threading with firm hand torque until completely seated against Rubber Friction Washer.
- 2. Attach antenna to NMO mount (sold separately) with firm hand torque.
- 3. Refer to Table 1 to determine desired frequency and cut length.
- 4. <u>Note:</u> Vehicle ground-plane variations will affect final tuned length and VSWR match. Always make <u>first cut</u> longer than referenced in Table 1. <u>The tuned length always includes the ball tip attached.</u>
- 5. Loosen the ball tip from the whip using a 1/16" hex wrench.
- 6. Measure the cut length "W" as shown in figure 1. The length includes ball tip.
- 7. Cut the whip longer than desired length using heavy-duty wire cutters.
- 8. During the tuning process, attach the ball tip to the top of the cut whip using hex wrench.
- Verify that reflected power is minimized for best performance at desired frequency using VSWR meter or similar device. If necessary, frequency tuning is achieved by cutting the whip in small incremental cuts until desired frequency match is verified.
- 10. Secured ball tip with hex wrench using firm hand torque.

<u>Automatic Car Wash Features:</u> - For optimal protection and extended reliability of the antenna and the NMO vehicle mount, <u>remove the whip only</u> from the antenna base (as shown in Figure 1) before entering automatic car wash. Before reinstallation, wipe the stud and base dry with a clean cloth. Attach whip to the antenna adapter with firm finger tight grip.



HG10382DU-GPS REV | © 2019 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.



HG10382DU-GPS



Environmental Specifications Temperature Operating Range

-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Dual Band Duplexed Antenna Kit with GPS 108-174 380-870 MHz NMO Mount/N Type Connectors from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

USA & Canada +1(800) 341-5266 | International +1(978) 682-6936 | L-com.com

7

L-com CAD Drawing

