

# 2.4 GHz 0dBi STUB "Rubber Duck" WLAN Antenna with RIGID RP-SMA Plug Connector

# HG2400RDR-RSP

# TIGE TOOK BIT TO

#### **Applications and Features**

#### Applications:

- 2.4 GHz ISM Band
- IEEE 802.11b, 802.11g Wireless LAN
- IEEE 802.11n (Pre-N, Draft-N, MIMO) Applications
- Factory WLAN installations
- Bluetooth<sup>®</sup>
- Wireless Video Systems
- Multipoint and Mobile Applications




- Better performance than most stock PC-Card antennas
- Rigid Stub "Rubber Duck" antenna
- Compact and easy to deploy
- Fits a wide range of wireless devices
- RoHS Compliant



#### **Description**

The HG2400RDR-RSP is a 2.4GHz 0dBi Omni-directional Stubby "rubber-duck" WiFi antenna. The antenna is a ¼ wave Monopole for excellent range and performance. It is ideally suited for IEEE 802.11b, 802.11g and 802.11n wireless LANs, Bluetooth®, factory WLAN installations and other WLAN applications requiring small, performance antennas.





# **Specifications**

#### **Electrical Specifications**

Frequency	2400-2500 MHz
Gain	0 dBi
Impedance	50 Ohm
VSWR	< 2.0


#### **Mechanical Specifications**

Weight	1.0 oz. (28 g)
Length	1.12" (28.5 mm)
Max. Diameter	0.31" (7.9 mm)
Finish	Matte Black/ Brass Connector
Connector	RP-SMA Plug Rigid Base



Operating Temperature	-20° C to 65° C (-4° F to 149° F)
Polarization	Vertical
Flame Rating	UL 94HB
RoHS Compliant	Yes

#### **Dimensions**



### **VSWR Test Report**



## **Guaranteed Quality**

This product is backed by L-com's Limited Warranty