

## HyperLink 2.4 GHz 3 dBi N-Male "Rubber Duck" Wireless LAN Antenna

Model: HG2403RD-NM

### Features

- Compact size, only 5.4" long
- Tilt and swivel design
- RP-TNC Connector
- 802.11b, 802.11g and Bluetooth® compatible



### Description

This compact 2.4GHz Omni directional "rubber-duck" WiFi antenna provides broad coverage and 3 dBi gain. It is a coaxial sleeve design with an omni-directional pattern. It is ideally suited for IEEE 802.11b and 802.11g wireless LANs, Bluetooth® and other WLAN applications.

Only 5.8" long, this flexible antenna features a tilt-and-swivel N-Type Male connector, allowing them to be used vertically, at a right angle, or any angle in-between.

### Specifications

#### Electrical Specifications

<b>Frequency</b>	2400-2500 MHz
<b>Gain</b>	3 dBi
<b>Impedance</b>	50 Ohm
<b>VSWR</b>	< 2.0
<b>Input Power</b>	55 Watts

#### Mechanical Specifications

<b>Weight</b>	1.4 oz. (40 g)
<b>Length</b>	5.8" (147 mm)
<b>Diameter</b>	0.5" (13 mm)
<b>Finish</b>	Matte Black
<b>Connector</b>	N-Type Male
<b>Operating Temperature</b>	-40° C to 85° C (-40° F to 185° F)

Polarization	Vertical
--------------	----------

Model: HG2403RD-NM

Antenna Gain Pattern

