

617-960 MHz / 1710-2700 MHz 6 / 6 dBi Gain MIMO Omnidirectional Antenna - Type N Female Connector, Polycarbonate Radome

## **HG62706DPU**



### **Features**

- · All weather operation
- Includes heavy duty steel mast mounting brackets
- · Lightweight polycarbonate radome
- · Integral N-Female connector

# **Applications**

- Supports low and midband LTE and 5G networks
- Point to Multipoint and Non Line of Sight (NLOS) Applications
- · Commercial grade design
- 360° Omnidirectional Pattern
- 4 to 6 dBi gain

600, 700, 800, 1800, 1900, 2100, 2600 Cellular Band Operation

## Description

The L-com HG62706DPU is a high performance 5G / LTE outdoor omnidirectional antenna specifically designed for cellular networks. L-coms HG62706DPU has 4 to 6 dBi gain and can be used to broadcast Cellular LTE signals. The HG62706DPU operates from 617 to 2700 MHz which is ideal for 5G, LTE, PCS, UMTS applications including LoRA, LTE-M, and NB-IOT. The Multi-Band design of the L-com HG62706DPU antenna eliminates the need to purchase different antennas for each frequency. This simplifies installations since the same antenna can be used for a wide array of telecommunication applications where wide coverage is desired.

The HG62706DPU from L-com has omnidirectional patterns with vertical polarization and features Type N connectors. The Type N connectorized HG62706DPU antenna from L-com is designed specifically for outdoor operation and is ideal for point to multipoint use in large open areas such as base station installations or large campuses. The included mounting bracket and hardware makes this antenna very easy to install. This 5G / LTE outdoor omnidirectional antenna just like our wide selection of superior quality RF parts, ship same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

### Configuration

Design
Band Type
Radiation Pattern
Polarization
Connector Type
Number of Ports

Omni Single Omni Directional Vertical N Female

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	617		2,700	MHz
Impedance		50		Ohms
Input Power			50	Watts

### Specifications by Band

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 617-960 MHz / 1710-2700 MHz 6 / 6 dBi Gain MIMO Omnidirectional Antenna - Type N Female Connector, Polycarbonate Radome HG62706DPU



617-960 MHz / 1710-2700 MHz 6 / 6 dBi Gain MIMO Omnidirectional Antenna - Type N Female Connector, Polycarbonate Radome

# **HG62706DPU**

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	0.617 to 0.96	1.71 to 2.7				GHz
Gain	6	6				dBi
Horizontal HPBW	360	360				Degrees
Vertical HPBW	40	25				Degrees
VSWR Max	2:1	2:1				

## **Mechanical Specifications**

Radome Material Polycarbonate

 Size

 Length
 35.1 in [891.54 mm]

 Width
 3.1 in [78.74 mm]

Mounting Mast Diameter 1.97 to 3.54 in [50.04 to 89.92 mm]

Weight 3.75 lbs [1.7 kg]

### **Environmental Specifications**

**Temperature** 

Operating Range -40 to +70 deg C Wind Survivability 124.27 MPH [199.99 KPH]

Humidity

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:

617-960 MHz / 1710-2700 MHz 6 / 6 dBi Gain MIMO Omnidirectional Antenna - Type N Female Connector, Polycarbonate Radome from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# **L-com CAD Drawing**

