

880 MHz to 960 MHz 13 dBi Yagi Antenna, 36in LMR400 coax with Type N Female Connector, Adjustable Polarization Fully Welded Aluminum



HG913P-NF

Features

- Aircraft Quality 6061-T6 Aluminum with 5/16" Elements with 360° Can be Installed for Either Vertical or Horizontal Polarization Fully Welded to a 1" Boom
- Powder-Coated Balck for Corrosion, Fade, and Ice-Build Up Resistance
- Comes with 36" LMR400 Pigtails with N-Type Female Connec-

Applications

- 900 MHz Cellular and GSM
- 900 MHz ISM Band & Wireless LAN Systems
- · Point to Multipoint & Non Line of Sight

- NLOS Applications
- RFID & SCADA
- LPWAN, LoRA, IoT, M2M

Description

The L-com 880 MHz to 960 MHz HG913P-NF Yagi Antenna ships the same day and is designed for the most rugged conditions. This 900 MHz antenna provides 13 dBi of gain and adjustable polarization. Equipped with an N-Female connector on a 36 in LMR400 pigtail, coaxial connections to a radio are simple and easy. The HG913P-NF is ideally suited for 900 MHz ISM bands. This 13 dBi antenna supports Land Mobile Radio for land transportation, utility, manufacturing, and petrochemical companies (oil and gas).

Measuring 43 inches long, the N-female HG913P-NF from L-com is manufactured using robust 5/16" aircraft quality aluminum elements. The HG913P-NF elements are completely welded to a 1" boom and painted black. This ensures performance and survivability in the toughest environments.

880 MHz to 960 MHz Yagi antennas from L-com are high-quality components backed by expert technical support and sales personnel. Like the other RF components at L-com, the 13 dBi HG913P-NF is in stock and ready to ship the same day.

Configuration

Design Yagi Band Type Single Radiation Pattern Directional Polarization Linear Cable Type I MR400 36 in [914.4 mm] Cable Length Connector Type N Female

Number of Ports

Housing Material and Plating Aluminum, Powder Coat

Electrical Specifications

Frequency Range 880 960 MHz Input VSWR 1.3:1 1.5:1 Impedance 50 Ohms 13 dBi Gain

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 880 MHz to 960 MHz 13 dBi Yagi Antenna, 36in LMR400 coax with Type N Female Connector, Adjustable Polarization Fully Welded Aluminum HG913P-



880 MHz to 960 MHz 13 dBi Yagi Antenna, 36in LMR400 coax with Type N Female Connector, Adjustable Polarization Fully Welded Aluminum



HG913P-NF

Input Power	150	Watts

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	880-928	928-960				MHz
Gain	12.5	13				dBi
Horizontal HPBW	42	40				Degrees
Vertical HPBW	38	35				Degrees
Front to Back Ratio	17	17				dB
VSWR Max	1.5:1	1.5:1				

Mechanical Specifications

Housing Material Aluminum
Housing Plating/Color Powder Coat

Size

 Length
 43 in [109.22 cm]

 Width
 7.1 in [180.34 mm]

 Height
 2.4 in [60.96 mm]

Mounting Mast Diameter 0.75 to 2 in [19.05 to 50.80 mm]

Weight 8 lbs [3.63 kg]

Environmental Specifications

Temperature

Operating Range -40 to +60 deg C
Storage Range -40 to +140 deg C
Wind Survivability 200 MPH [321.87 KPH]

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

880 MHz to 960 MHz 13 dBi Yagi Antenna, 36in LMR400 coax with Type N Female Connector, Adjustable Polarization Fully Welded Aluminum from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line



880 MHz to 960 MHz 13 dBi Yagi Antenna, 36in LMR400 coax with Type N Female Connector, Adjustable Polarization Fully Welded Aluminum



HG913P-NF

which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

