

Coaxial Adapter, SMA Female / SMB Plug



LCAD30008

Configuration

- SMA Female Connector 1
- SMB Plug Connector 2

Features

- Provides Between Series SMA to SMB Connections
- · Operates to 4 GHz
- Applications

- Impedance 50 Ohm
- · Straight Body Geometry
- Max VSWR of 1.3:1
- · Gold Plated Center Contacts

Description

These L-com RF Coaxial Adapters are used to interface between SMA to SMB with coaxial connections. The LCAD30008 is a straight adapter with a female to plug configuration. This Coaxial Adapter, SMA Female / SMB Plug is made from brass and has a nickel finish.&&An SMA interface design is defined by Mil-STD-348A and has many popular features including a threaded coupling method with a robust center contact and outer conductor interface. SMA's generally work up to 18GHz and are a cost effective way of insuring a highly dependable RF Coaxial connection.&&The SMB interface is smaller than an SMA and uses a snap on connection. An important difference to note is that the SMB Jack (female) interface design has a Male center contact and the SMB Plug (Male) design uses a female socket for the center pin. SMB connectors generally have a maximum operating frequency of 4 GHZ and are available in 50 Ohm and 75 Ohm impedances.&&L-com's RF Coaxial and Triaxial adapters are in stock and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.3:1	
Operating Voltage (AC)			335	Vrms

Mechanical Specifications

 Size
 Length
 0.64in
 16.26mm]

 Width
 0.25in
 [6.35mm]

Description	Connector 1	Connector 2
Туре	SMA Female	SMB Plug
Polarity	Standard	Standard



Coaxial Adapter, SMA Female / SMB Plug



LCAD30008

Material Specifications

Connector 1		Connector 2	
Material	Plating	Material	Plating
SMA Female		SMB Plug	
Beryllium Copper	Gold	Beryllium Copper	Gold
PTFE		PTFE	
Brass	Nickel		
Brass	Nickel	Brass	Nickel
		Brass	Nickel
	Material SMA Female Beryllium Copper PTFE Brass	Material Plating SMA Female Beryllium Copper Gold PTFE Brass Nickel	MaterialPlatingMaterialSMA FemaleSMB PlugBeryllium CopperGoldBeryllium CopperPTFEPTFEBrassNickelBrassNickelBrass

Environmental Specifications

Temperature

Operating Range -65°C to +165°C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Coaxial Adapter, SMA Female / SMB Plug from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

THIRD-ANGLE PROJECTION THE INCORMATION AND IS ESSENTING THE INCORMATION AND IS ESSENTING AND ALL RIGHTS RESERVED. SHEET 1 OF 1 SCALE N/A
THRD-ANGLI THE INFORMATION THE INFORMATION THE THROW THROW
Net
l lo
.64 [16.31] .64 [16.31] .64 .64 .62 .64 .64 .64 .65 .64 .65 .65 .65
1/4-36UNS-2A
1/4-36UNS-2A
į.