

Coaxial Adapter, SMA Female / SMB Jack



LCAD30009

Configuration

- SMA Female Connector 1
- SMB Jack Connector 2

Features

- Provides Between Series SMA to SMB Connections
- · Operates to 4 GHz
- **Applications**

- Impedance 50 Ohm
- Straight Body Geometry
- Max VSWR of 1.46:1
- · Gold Plated Center Contacts

Description

These L-com RF Coaxial Adapters are used to interface between SMA to SMB with coaxial connections. The LCAD30009 is a straight adapter with a female to jack configuration. This Coaxial Adapter, SMA Female / SMB Jack is made from brass and has a nickel finish.&An SMA interface design is defined by Mil-STD-348A and has many popular features including a threaded coupling method with a robust center contact and outer conductor interface. SMA's generally work up to 18GHz and are a cost effective way of insuring a highly dependable RF Coaxial connection.&The SMB interface is smaller than an SMA and uses a snap on connection. An important difference to note is that the SMB Jack (female) interface design has a Male center contact and the SMB Plug (Male) design uses a female socket for the center pin. SMB connectors generally have a maximum operating frequency of 4 GHZ and are available in 50 Ohm and 75 Ohm impedances.&&L-com's RF Coaxial and Triaxial adapters are in stock and ship same day.

Electrical Specifications

Minimum	Typical	Maximum	Units
DC		4	GHz
		1.46:1	
		375	Vrms
ge (AC)		375	Vrms
nce		6	mOhms
nce		1	mOhms
5,000			MOhms
	ge (AC)	ge (AC)	DC 4 1.46:1 375 ge (AC) 375 nce 6 nce 1

Mechanical Specifications

 Size
 0.61in
 15.49mm]

 Width
 0.25in
 [6.35mm]

Description	Connector 1	Connector 2
Туре	SMA Female	SMB Jack



Coaxial Adapter, SMA Female / SMB Jack



LCAD30009

Polarity	Standard	Standard

Material Specifications

	Connector 1		Connector 2	
Description	Material	Plating	Material	Plating
Туре	SMA Female		SMB Jack	
Contact	Phosphor Bronze	Gold	Phosphor Bronze	Gold
Insulation	PTFE		PTFE	
Outer Conductor	Brass	Nickel	Brass	Gold
Body	Brass	Nickel	Brass	Nickel

Environmental Specifications

Temperature

Operating Range -55°C to +155°C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Coaxial Adapter, SMA Female / SMB Jack from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

